

500V N-Channel Planar MOSFET

MOSFET

Metal Oxide Semiconductor Field Effect Transistor

500V N-Channel Planar MOSFET

500V N-Channel Planar MOSFET Power Transistor

HRH18N50ANx Data Sheet

Rev. 2023 V1.1



500V N-Channel Planar MOSFET

Description

500V N-Channel Planar MOSFET



HRH18N50ANx is HRM high voltage MOSFET family based on advanced planar stripe DMOS technology. This advanced MOSFET family has optimized on-state resistance, and also provides superior switching performance and higher avalanche energy strength. This device family is suitable for high efficiency switch mode power supplies.

Features

- $R_{DS(on)}=0.28\Omega$ @ $V_{gs}=10V$, $I_d=9A$
- Low gate Charge(typical 49.8nC)
- Low C_{rss} (typical 4.3pF)
- Fast switching capability
- 100% avalanche tested
- Improved dv/dt capability

Applications

- Switch Mode Power Supply
- Uninterruptible Power Supply (UPS)
- TV Power
- A dapter/Charger



Key Performance Parameters

Parameter	Value	Unit
V_{DS}	500	V
$R_{DS(on),typ}$	0.28	Ω
$Q_{g,typ}$	49.8	nC
I_D	18	A
$I_{D,pulse}$	72	A

Device Marking and Package Information

Device	Package	Marking
HRH18N50ANF	TO-220F	H18N50ANF
HRH18N50ANB	TO-263	H18N50ANB
HRH18N50ANP	TO-220	H18N50ANP
HRH18N50ANV	TO-3P	H18N50ANV
HRH18N50ANW	TO-247	H18N50ANW

Absolute Maximum Ratings T _C = 25°C, unless otherwise noted				
Parameter		Symbol	Value	Unit
Drain-Source Voltage(V _{GS} =0V)		V _{DS}	500	V
Continuous Drain Current ¹⁾	T _C = 25°C	I _D	18	A
	T _C = 100°C		10.8	
Pulsed Drain Current ²⁾		I _{D,pulse}	72	A
Gate-Source Voltage		V _{GS}	±30	V
Single Pulse Avalanche Energy ³⁾		E _{AS}	1215	mJ
Peak Diode Recovery dv/dt ⁴⁾		dv/dt	5	V/ns
Power Dissipation For TO-220F		P _D	75	W
Power Dissipation For TO-220/3P/247/263			189	
Continuous Diode Forward Current		I _S	18	A
Diode Pulsed Current ²⁾		I _{S,pulse}	72	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55~+150	°C

Thermal Resistance For TO-220F			
Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	1.65	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient	R_{thJA}	80	

Thermal Resistance For TO-220/3P/247/263			
Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	0.66	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient	R_{thJA}	62	

Notes

- 1) Limited by maximum junction temperature.
- 2) Repetitive Rating: Pulse width limited by maximum junction temperature.
- 3) $L=7.5\text{mH}$, $I_D=18\text{A}$, $R_G=25\Omega$, $V_{DD}=100\text{V}$, Start $T_J=25^\circ\text{C}$.
- 4) $I_{SD} \leq 18\text{A}$, $di/dt \leq 100\text{A}/\mu\text{s}$, $V_{DD} \leq BV_{DSS}$, Start $T_J=25^\circ\text{C}$.

Electrical Characteristics T _J = 25°C, unless otherwise noted						
Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Characteristics						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = 250μA	500	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 500V V _{GS} = 0V, T _J = 25°C	--	--	1	μA
		V _{DS} = 500V, V _{GS} = 0V, T _J = 150°C	--	--	100	
Gate-Source Leakage Current	I _{GSS}	V _{GS} = ±30V	--	--	±100	nA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	3	--	5	V
Drain-Source On-State-Resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 9A	--	0.28	0.33	Ω
Gate Resistance	R _G	f = 1.0MHz open drain	--	1.5	--	Ω
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = 25V f = 1.0MHz	--	3041	--	pF
Output Capacitance	C _{oss}		--	233	--	
Reverse Transfer Capacitance	C _{rss}		--	4.3	--	
Total Gate Charge	Q _g	V _{DD} = 400V, I _D = 18A V _{GS} = 10V	--	49.8	--	nC
Gate-Source Charge	Q _{gs}		--	18.2	--	
Gate-Drain Charge	Q _{gd}		--	12.3	--	
Gate Plateau Voltage	V _{plateau}		--	5.9	--	V
Turn-on Delay Time	t _{d(on)}	V _{DD} = 250V, I _D = 18A R _G = 10Ω, V _{GS} = 10V	--	28	--	ns
Turn-on Rise Time	t _r		--	47	--	
Turn-off Delay Time	t _{d(off)}		--	57	--	
Turn-off Fall Time	t _f		--	40	--	
Drain-Source Body Diode Characteristics						
Body Diode Forward Voltage	V _{SD}	T _J = 25°C, I _{SD} = 18A V _{GS} = 0V	--	--	1.2	V
Reverse Recovery Time	t _{rr}	V _R = 400V I _F = 18A, di _F /dt = 100A/μs	--	449	--	ns
Reverse Recovery Charge	Q _{rr}		--	4.8	--	μC

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted




Figure 1. Transient Thermal Impedance For TO-220F




Figure 2. Transient Thermal Impedance For TO-220/3P/247/263




Figure 3. Safe Operation Area For TO-220F




Figure 4. Safe Operation Area For TO-220/3P/247/263




Figure 5. Output Characteristics




Figure 6. Transfer Characteristics

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted




Figure 7. On-Resistance vs Drain Current




Figure 8. Capacitance




Figure 9. Gate Charge




Figure 10. Body Diode Forward Voltage




Figure 11. Breakdown Voltage vs Junction Temperature




Figure 12. On-Resistance vs Temperature

Figure A: Gate Charge Test Circuit and Waveform




Figure B: Resistive Switching Test Circuit and Waveform






Figure C: Unclamped Inductive Switching Test Circuit and Waveform




Outlines TO-263 Package




SYMBOL	MIN	NOM	MAX	SYMBOL	MIN	NOM	MAX
A	4.37	4.57	4.77	E5	7.06	---	---
A1	1.22	1.27	1.42	e	2.54 BSC		
A2	2.49	2.69	2.89	H	14.70	15.10	15.50
A3	0	0.13	0.25	H2	1.07	1.27	1.47
b	0.7	0.81	0.96	L	2.00	2.30	2.60
b1	1.17	1.27	1.47	L1	1.40	1.55	1.70
c	0.30	0.38	0.53	L4	0.25 BSC		
D1	8.50	8.70	8.90	θ	0°	5°	9°
D4	6.60	---	---	Θ	0°	--	8°
E	9.86	10.16	10.36	$\Theta 1$	1°	3°	5°

Outlines TO-220 Package





SYMBOL	MIN	NOM	MAX
A	4.37	4.535	4.7
A1	1.25	1.3	1.4
A2	2.2	2.4	2.6
b	0.7	---	0.95
b1	1.17	---	1.47
c	0.45	0.5	0.6
D	15.1	15.65	16.1
D1	8.8	9.15	9.4
D2	11.8	---	---
E	9.7	9.95	10.3
E1	7	---	---
e	2.54 BSC		
e1	5.08 BSC		
H1	6.25	6.5	6.85
L	12.75	13.29	13.8
L1	---	---	3.5
ΦP	3.4	3.67	3.8
Q	2.6	---	3

Outlines TO-220F Package



SYMBOL	MIN	NOM	MAX
A	4.5	4.7	4.9
A1	2.34	2.54	2.74
A3	2.56	2.76	2.96
b	0.7	---	0.95
b1	1.18	---	1.43
b2	---	---	1.55
c	0.4	0.5	0.65
D	15.57	15.87	16.17
D1	15.35	15.675	15.95
D2	9.6	9.875	10.15
E	9.96	10.16	10.36
e	2.54 BSC		
H1	6.48	6.68	6.88
L	12.68	12.98	13.28
L1	---	---	3.5


Outlines TO-3P Package



SYMBOL	MIN	NOM	MAX
A	4.6	4.8	5.0
A1	1.2	1.4	1.6
b	0.8	1	1.2
b1	2.8	3	3.2
b2	1.8	2	2.2
c	0.5	0.6	0.7
c1	1.45	1.55	1.65
D	15.45	15.65	15.85
E	13.7	13.9	14.1
E1	3.3REF		
E2	3.2REF		

SYMBOL	MIN	NOM	MAX
E3	12.9REF		
F1	13.4	13.6	13.8
F2	9.4	9.6	9.8
L	39.7	39.9	40.1
L1	23.2	23.4	23.6
L2	19.7	19.9	20.1
ø	6.9	7	7.1
G	4.6	4.8	5.0
e	5.45TYP		
H	5.0REF		
h	0.0	0.15	0.3

Outlines TO-247 Package



SYMBOL	MIN	NOM	MAX
A	4.9	5	5.1
A1	2.31	2.41	2.51
A2	1.9	2	2.1
a	0	---	0.15
a'	0	---	0.15
b	1.16	---	1.26
b1	1.15	1.2	1.22
b2	1.96	---	2.06
b3	1.95	2	2.02
b4	2.96	---	3.06
b5	2.96	3	3.02
b6	---	---	2.25
b7	---	---	3.25
c	0.59	---	0.66
c1	0.58	0.6	0.62
D	20.9	21	21.1
D1	16.25	16.55	16.85

SYMBOL	MIN	NOM	MAX
D2	1.05	1.17	1.35
E	15.7	15.8	15.9
E1	13.1	13.3	13.5
E2	4.4	4.5	4.6
E3	2.4	2.5	2.6
e	5.436 BSC		
L	19.8	19.92	20.1
L1	---	---	4.3
M	0.35	---	0.95
P	3.4	3.5	3.6
P1	7	---	7.4
P2	2.4	2.5	2.6
Q	5.6	---	6
S	6.05	6.15	6.25
T	9.8	---	10.2
U	6	---	6.4

Disclaimer

HRM has made reasonable commercial efforts to ensure that the information given in this datasheet is correct. However, it must clearly be understood that such information is for guidance only and does not constitute any representation or form part of any offer or contract.

For documents and material available from this datasheet, HRM does not warrant or assume any legal liability or responsibility for the accuracy, completeness, or usefulness of any information, product, technology or process disclosed hereunder.

HRM reserves the rights to at its own discretion to make any changes or improvements to this datasheet. Unless said datasheet is incorporated into the formal contract, any customer should not rely on the information as any specification or product parameters duly committed by HRM. Customers are hereby advised to verify that the information contained herein is current and complete before the entering of any contract or acknowledgement of any purchase order. Accordingly, all products specified hereunder shall be sold subject to HRM's terms and conditions supplied at the time of order acknowledgement. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessarily performed.

HRM does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information contained herein shall be only permissible if such reproduction is without any modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. HRM is not responsible or liable for such altered documentation.

Resale of HRM's products with statements different from or beyond the parameters stated by HRM for that product or service voids all express or implied warranties for the associated HRM's product or service and is unfair and deceptive business practice. HRM is not responsible or liable for any such statements.

HRM's products are not authorized for use as critical components in life support devices or systems without the express written approval of HRM. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.