




used for: D-SUB



NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREY
3. CONTACTS: COPPER ALLOY
4. PLATING: GOLD FLASH over NICKEL
5. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
7. CONNECTOR IS PART MARKED: 161A13539X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance		
2013	date	name
drawn	11.04.	Henneboel
appd.	12.04.	Fischer
norm	DIN 41652	
d-old		

scale:	2:1		
material:	SEE NOTES		
title:	D-SUB IDC-Male for flat cable, 50 pos.		
dwg no:	AutoCAD	DIN-A	
16K1A3227		3	
		sh: 1/1	
part no:	161A13539X		

CONEC