






Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20m Ω Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M Ω Min
Operation Temperature:-40 $^{\circ}$ c to +105 $^{\circ}$ c

Contact Material:Copper Alloy
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 260 $^{\circ}$ C $\pm 5^{\circ}$ C 5S



P = With Post

默认 = W/O Post

Ordering Information

PM 254	-	*	-	N	-	S	-	*	-	**	-	P
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type Z-直插 W-弯插 S-立插 W=弯插	Length (Plastic) (mm)	Contact G0:Gold G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Plating Flash	Post (mm)						

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司			
					DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核	产品名称	2.54双排 排母 贴片(塑高8.5)	版本	A
			X. X	± 0.30	CHECK	TITLE		REV.	
			X. XX	± 0.20	批 准	产品料号	PM254-2-N-S-8.5-XX (L9.1)	单 位	mm
			X. XXX	± 0.10	APPROVAL	PART NO.		UNITS	
			Angle	$\pm 3.0^{\circ}$	比 例	材料		页 次	1/1
					SCALE			SHEET	
					投 影				
					Projection				