





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A1	REVISED PER ECO-09-024927	07NOV09	KK	AEG
			A2	REVISED PER ECO-12-011709	26JUN12	RW	SY



SECTION B-B
SCALE 20:1



SECTION A-A
SCALE 20:1

1. .000100 MIN THK BRIGHT TIN/LEAD OVER
.000050 MIN THK NICKEL OVER ENTIRE CONTACT.


2. MATING POST LENGTH ACCEPTED:
SINGLE ROW HOUSINGS .210-.323
DOUBLE ROW HOUSINGS .225-.323

3. GOLD FLASH IN CRIMP AREA,
.000100 MIN TIN ON THE MATING AREA, BOTH OVER
.000050 MIN THK NICKEL ON ENTIRE CONTACT.

4. PARTS ARE NOT COATED WITH ANTI-FRETTING LUBE. THERE
IS A DISTINCT POSSIBILITY OF FRETTING CORROSION. THESE
PARTS ARE NOT RECOMMENDED FOR USE WHERE FRETTING
CORROSION IS A POSSIBILITY.

5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6. GOLD PLATING MAY OR MAY NOT BE PRESENT ON BOTTOM OF THE CRIMP
BARREL IN THIS AREA



SECTION C-C
SCALE 20:1

5	OBSOLETE	3	1761852-2
		1	1761852-1
		FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S. WAITMAN	18APR05	 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: INCHES			CHK J. GERACE	18APR05	NAME RECEPTACLE CONTACT, HIGH PRESSURE —				
			APVD M. WALMSLEY	18APR05					
			PRODUCT SPEC 108-9024		SIZE A2				
			APPLICATION SPEC 114-16015						CAGE CODE 00779
			MATERIAL PHOS BRONZE						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —			WEIGHT —		RESTRICTED TO —				
FINISH SEE TABLE			CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1	REV A2	