


PIN RECEPTACLES

FOR 0,56 - 0,86 DIAMETER PINS AND 0,64 SQUARE PINS

0291

0291-0-15-XX-16-XX-10-0


Hex press-fit in 1,7 plated through-hole



0293

0293-0-15-XX-16-XX-10-0


Press-fit in 1,7 mounting hole



0287

0287-0-15-XX-16-XX-10-0


Solder mount in 1,65 min. mounting hole
Also available on 8mm wide carrier tape:
3,250 parts per 330mm reel
Order as: 0287-0-57-XX-16-XX-10-0



0285

0285-0-15-XX-16-XX-10-0


Solder mount in 1,65 min. mounting hole



0284

0284-0-15-XX-16-XX-10-0


Solder mount in 1,78 min. mounting hole



8114

8114-0-15-XX-16-XX-04-0


Press-fit from underside of pc board into 1,65 mounting hole



0407

0407-0-15-XX-16-XX-04-0


Press-fit in 1,68 mounting hole



0415

0415-0-15-XX-16-XX-10-0


Solder mount in 1,6 min. mounting hole
Also available on 24mm wide carrier tape:
1,500 parts per 330mm reel
Order as: 0415-0-57-XX-16-XX-10-0



0303

0303-0-19-XX-16-XX-10-0


Press-fit in 1,7 mounting hole
Wire Crimp Termination. Accepts wire sizes 26 AWG Max. / 30 AWG Min.



0306

0306-0-19-XX-16-XX-10-0


Wire Crimp Termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



0273

0273-0-15-XX-16-XX-10-0


Press-fit in 1,98 mounting hole



7520

7520-0-15-XX-16-XX-10-0

Press-fit in 1,68 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$

Diameters: $\pm 0,051$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 5,04µm TIN/LEAD OVER NICKEL

◆ **80** 5,04µm TIN OVER NICKEL (RoHS)

◆ **15** 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 5,04µm TIN/LEAD OVER NICKEL

◆ **80** 5,04µm TIN OVER NICKEL (RoHS)

◆ **27** 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#16 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com