






Detail
Scale 5:1




TE PN	Part
3-6437630-5	F4TN0904
3-6437630-6	F4TPA0904


Date Code Printing
last digit of year
A-L = January to December
Day




ALCO
F4TN0904
6A AC 250V
ON - ON
Model No.
Rating
SW. Funct.



Panel Cutout



Panel Cutout
using Ring




Nut




1,5 thick

Ring



1 thick

L washer



0.63 thick

Notes:

Operating temperature -20°C to +70°C

All materials and finishes comply with RoHS directive

Materials Chart

1	Case	Polyester Resin	
2	F Contact	99.98% silver + C3602BD	Ep-Cu/Ni3,AuFb
3	Common	C3602BD	Ep-Cu/Ni3,AuFb
4	Frame	SUS	
5	Bushing	C3602BD	Ep-Cu/Ni3b
6	Actuator	C3602BD	Ep-Cu/Ni3,Cr1b
7	Nut	C3602BD	Ep-Cu/Ni3b
8	Ring	SPCC	Ep-Fe/Cu2,Ni3b
9	L washer	SK-5	Ep-Fe/Cu2,Ni4b
PART NO:	PART NAME:	MATERIAL/SURFACE:	OPTIONAL DESCRIPTION
PART LIST			

TOLERANCES UNLESS OTHERWISE SPECIFIED ACCORDING TO ISO 8015 and ISO 2768-1				DIMENSIONS: mm	
test dimen. / Prüfmaß: □□□, auxiliary dimen. / Hilfsmaß: (), theor. dimen. / theor. Maß: □□□, production control dimen. / Fertigungs-kontrolmaß: [] , dimen. for measure. technology / messtechn. rel. Maß: [] ,					
		DEPARTMENT	D&E		
		DRAWER	03.01.2007 SA008713		
		CHECKED			
		APPROVED			
ECR-NO:		DATE	NAME	INFO	
SCALE:		DATE	NAME	INFO	
DWG NO:				DWG NO:	
Toggle Switch quad. pole				C=1968517	
Standard Lever				Customer Drawing	
REPLACEMENT FOR:		DWG LOC NO:	IF	SHEET: 1 OF 1	REVISION: A A 2
THIS DRAWING IS A CONTROLLED DOCUMENT. HANDWRITTEN CHANGES ARE NOT ALLOWED					