


# PIN RECEPTACLES

FOR .065" - .082" DIAMETER PINS

## 0394

0394-0-15-XX-07-XX-10-0


Solder mount in .120 min. mounting hole



## 0393

0393-0-15-XX-07-XX-10-0


Solder mount in .144 min. mounting hole



## 0391

0391-0-15-XX-07-XX-10-0


Solder mount in .159 min. mounting hole



## 9016

9016-0-15-XX-07-XX-10-0


Press-fit in .131 mounting hole



## 0493

0493-0-15-XX-07-XX-10-0


Press-fit in .144 mounting hole



## 0490

0490-0-15-XX-07-XX-04-0


Press-fit in .144 mounting hole



## 0616

0616-0-18-XX-07-XX-10-0


Press-fit in .144 mounting hole  
Accepts wire sizes up to .035" dia.



## 0387

0387-0-15-XX-07-XX-04-0


Solder mount in .063 min. mounting hole



## 0370

0370-0-19-XX-07-XX-10-0


Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



## 4040

4040-0-19-XX-07-XX-10-0


Wire crimp termination. Accepts wire sizes 16 AWG Max. / 20 AWG Min.



## 0491

0491-0-19-XX-07-XX-04-0


For horizontal wire termination



## 9214

9214-0-15-XX-07-XX-10-0

Solder mount in .083 min. mounting hole



### SPECIFICATIONS:

**Shell Material:** Brass Alloy 360, 1/2 Hard

**Contact Material:** Beryllium Copper Alloy 172, HT

**Dimensions:** Inches

**Tolerances On:** Lengths:  $\pm .005$

Diameters:  $\pm .002$

Angles:  $\pm 2^\circ$



**ORDER CODE:** XXXX - X - 1X - XX - 07 - XX - XX - 0

**BASIC PART #**

**SPECIFY SHELL FINISH:**

- 01 200  $\mu$ " TIN/LEAD OVER NICKEL
- ◆ 80 200  $\mu$ " TIN OVER NICKEL (RoHS)
- ◆ 15 10  $\mu$ " GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**

- 01 200  $\mu$ " TIN/LEAD OVER NICKEL
- ◆ 80 200  $\mu$ " TIN OVER NICKEL (RoHS)
- ◆ 27 30  $\mu$ " GOLD OVER NICKEL (RoHS)

**SELECT CONTACT:**

**#07 CONTACT (DATA ON PAGE 261)**

(For alternate contact choices, see group H on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com