








PCB.WELDING DRAWING (TOLERANCE:±0.05)



SECTION A-A



Technical Index:

- 1.Temperature range: -25°C~+85°C.
- 2.Rated voltage: 600V, AC, DC.
- 3.Rated current: 5.0A AC, DC.
- 4.Contact resistance: ≤20mΩ .
- 5.Withstanding voltage: 1500V AC/minute.
- 6.Insulation resistance: ≥1000MΩ.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

型号	CKT	A	B
A300E1L2-2B2P12	2*1	0.00	6.00
A300E1L2-2B4P12	2*2	3.00	9.00
A300E1L2-2B6P12	2*3	6.00	12.00
A300E1L2-2B8P12	2*4	9.00	15.00
A300E1L2-2B10P12	2*5	12.00	18.00
A300E1L2-2B12P12	2*6	15.00	21.00
A300E1L2-2B14P12	2*7	18.00	24.00
A300E1L2-2B16P12	2*8	21.00	27.00
A300E1L2-2B18P12	2*9	24.00	30.00
A300E1L2-2B20P12	2*10	27.00	33.00
A300E1L2-2B22P12	2*11	30.00	36.00
A300E1L2-2B24P12	2*12	33.00	39.00

2	端子Contact	黄铜	N*1	表面镀锡
1	基座Wafer	PA66(UL94 V-0)	1	黑色
序号	名称	材料	数量	备注

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.20	X.* ±10°	PART NO.	TITLE:	
.XX ±0.10	.X* ± 8°	A300E1L2-2BXP12		MX3.0MM 双排直针带扣带定位柱
.XXX ±0.05	.XX* ± 5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---		SCALE	SHEET
			N:A	1/1