



1. Configuration & Dimensions: (Unit:mm)



SYMBOL	A	B	C	D	E	F	Q'Ty/Disc
ADT14B70	17.5Max	19.0Max	12.0Max	4.5±0.5	8.5±0.5	0.9±0.1	130

2. Electrical Schematics :



3. Part Number Code

ADT 14 B 70 X 600
 A B C D E F

A: Series Name Choke Coil
 B: Dimensions(mm) 14: 17.5 Max
 C: Materials B=The base
 D: Thickness(mm) 70: 12.0 Max
 E: Tolerance X: Min
 F: Inductance 600=60uH

4. Electrical Apecification &Test Instrumenis :

Part Number	Inductance (uH)	Tolerance	Test Frequency (KHz)	DC Resistance (mΩ) Max	Rated DC Current (A)Max
ADT14B70X600	60	Min	1KHz/0.25V	25	3