


**Version history**

Current version	Date	Author	Change description

## Metallized polyester film interference suppression capacitor (Class X2, Temperature Humidity Bias (THB) series)

### ■ Outline Drawing



### ■ Features

- Metallized polyester with series construction
- High stability of capacitance under severe ambient condition, such as high humidity and high temperature
- Excellent active and passive flame resistant abilities
- For connection in series with the mains and capacitive divider power supply, such as energy meter, LED driver etc.

### ■ Safety Approvals

•		CQC	IEC 60384-14:2013, X2, 305Vac, 0.01μF~2.2μF, 40/105/56/B Certificate No.: CQC03001002873
•		ENEC-SEMKO	EN 60384-14:2013+A1:2016, X2, 305Vac, 0.01μF~2.2μF, 40/105/56/B Certificate No.: SE/0366-5C
•		UL-CUL	UL60384-14:2014, CSA E60384-14:09, X2, 305Vac, 0.01μF~2.2μF, 40/105/56/B File No.: E186600, CCN: FOWX2/8

### ■ Specifications

Class	X2		
Climatic Category/Passive Flammability Category	40/105/56/B		
Operating Temperature Range	-40°C ~ +105°C		
Rated Voltage ( $U_R$ )	305Vac, 50/60Hz		
Maximum continuous DC voltage	560Vdc		
Capacitance Range	0.010μF ~ 2.2μF		
Capacitance Tolerance	±10%(K), ±20%(M)		
Voltage Proof	Between Terminals		4.3 $U_R$ (dc), 2s
	Between Terminals To Case		2 120Vac, 1min
Insulation Resistance	$R \geq 15\ 000M\Omega$ , $C_N \leq 0.33\mu F$ (20°C, 100V, 1min) $RC_N \geq 5\ 000s$ , $C_N > 0.33\mu F$		
Dissipation Factor	$0.010\mu F \leq C_N \leq 1.0\mu F$	$\leq 80 \times 10^{-4}$ (1kHz, 20°C)	$\leq 150 \times 10^{-4}$ (10kHz, 20°C)
	$1.0\mu F < C_N$	$\leq 80 \times 10^{-4}$ (1kHz, 20°C)	-----
THB test (Damp heat test with loading)	Temperature: 85°C±2°C; Humidity: 85%RH±2% RH Voltage: 240Vac, 50Hz; Duration: 1 000h		
	Capacitance change ( $\Delta C/C$ ): ≤10% Dissipation factor change ( $\Delta \tan \delta$ ): ≤0.5% (1kHz) Insulation resistance: ≥50% of the rated value		



## ■ Part number system

The 15 digits part number is formed as follow:

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
C	2	6												

Digit 1 to 3      Series code

C26= MKT61

Digit 4 to 5      A.C. rated voltage

Q2=305V   P2=275V

Digit 6 to 8      Rated capacitance value

For example :  $103 = 10 \times 10^3 \text{ pF} = 0.01 \mu \text{F}$

Digit 9      Capacitance tolerance

$K = \pm 10\%$ ,  $M = \pm 20\%$

Digit 10      Pitch

4=10.0mm   6=15.0mm   9=22.5mm

B=27.5mm   F=37.5mm

Digit 11      Internal use

Digit 12 to 15      Lead form and packaging code

**Table1 Lead form and packaging code**

Digit 12		Digit 13		Digit 14		Digit 15	
code	explanation	code	explanation	code	explanation	code	explanation
A	ammo-pack	3	F=7.5mm	0	Straight	1	each cap. among two consecutive holes P3=12.7mm, H=18.5mm (For P=7.5mm) P3=25.4mm; H=18.5mm (For pitch=10/15mm) (Detail parameter refer to page 11)
		4	F=10.0mm			5	
		6	F=15.0mm				
C	straight lead "C" in the figure above	code	explanation			0	Length tolerance $\pm 0.5\text{mm}$ or standard length Length tolerance $\pm 0.3\text{mm}$
		00	standard lead length (18mm~26mm)	45	lead length 4.5mm		
		40	lead length 4.0mm	38	lead length 3.8mm		
		35	lead length 3.5mm	32	lead length 3.2mm		

Note: Recommend short lead due to long lead could deform easily.



## ■ Dimensions(mm)

305Vac							305Vac						
C <sub>N</sub> ( $\mu$ F)	W	H	T	P	d	Part number	C <sub>N</sub> ( $\mu$ F)	W	H	T	P	d	Part number
0.010	13.0	9.0	4.0	10.0	0.6	C26Q2103-40****	0.10	26.5	15.0	6.0	22.5	0.8	C26Q2104-90****
0.012	13.0	9.0	4.0	10.0	0.6	C26Q2123-40****	0.12	26.5	15.0	6.0	22.5	0.8	C26Q2124-90****
0.015	13.0	9.0	4.0	10.0	0.6	C26Q2153-40****	0.15	26.5	15.0	6.0	22.5	0.8	C26Q2154-9S****
0.018	13.0	11.0	5.0	10.0	0.6	C26Q2183-40****	0.18	26.5	15.0	6.0	22.5	0.8	C26Q2184-9S****
0.022	13.0	11.0	5.0	10.0	0.6	C26Q2223-40****	0.22	26.5	15.0	6.0	22.5	0.8	C26Q2224-9S****
0.027	13.0	11.0	5.0	10.0	0.6	C26Q2273-40****	0.27	26.5	16.0	7.0	22.5	0.8	C26Q2274-9S****
0.033	13.0	12.0	6.0	10.0	0.6	C26Q2333-40****	0.33	26.5	16.0	7.0	22.5	0.8	C26Q2334-9S****
0.039	13.0	12.0	6.0	10.0	0.6	C26Q2393-40****	0.39	26.5	17.0	8.5	22.5	0.8	C26Q2394-9S****
0.047	13.0	12.0	6.0	10.0	0.6	C26Q2473-40****	0.47	26.5	17.0	8.5	22.5	0.8	C26Q2474-9S****
0.056	13.0	13.0	7.0	10.0	0.6	C26Q2563-40****	0.56	26.5	18.5	10.0	22.5	0.8	C26Q2564-9S****
0.068	13.0	14.0	8.0	10.0	0.6	C26Q2683-40****	0.68	26.5	18.5	10.0	22.5	0.8	C26Q2684-9S****
0.010	17.5	9.5	5.0	15.0	0.6	C26Q2103-60****	0.82	26.5	20.0	11.0	22.5	0.8	C26Q2824-9S****
0.012	17.5	9.5	5.0	15.0	0.6	C26Q2123-60****	1.0	26.5	22.0	12.0	22.5	0.8	C26Q2105-9S****
0.015	17.5	9.5	5.0	15.0	0.6	C26Q2153-60****	1.2	26.5	23.0	13.5	22.5	0.8	C26Q2125-9S****
0.018	17.5	9.5	5.0	15.0	0.6	C26Q2183-60****	1.5	26.5	24.5	15.5	22.5	0.8	C26Q2155-9S****
0.022	17.5	9.5	5.0	15.0	0.6	C26Q2223-60****	1.5	26.5	29.5	14.5	22.5	0.8	C26Q2155-9A****
0.027	17.5	9.5	5.0	15.0	0.6	C26Q2273-60****	0.39	32.0	18.0	9.0	27.5	0.8	C26Q2394-B0****
0.033	17.5	9.5	5.0	15.0	0.6	C26Q2333-60****	0.47	32.0	18.0	9.0	27.5	0.8	C26Q2474-B0****
0.039	17.5	11.0	5.0	15.0	0.6	C26Q2393-60****	0.56	32.0	18.0	9.0	27.5	0.8	C26Q2564-BS****
0.047	17.5	11.0	5.0	15.0	0.6	C26Q2473-60****	0.68	32.0	18.0	9.0	27.5	0.8	C26Q2684-BS****
0.056	17.5	11.0	5.0	15.0	0.6	C26Q2563-60****	0.82	32.0	20.0	11.0	27.5	0.8	C26Q2824-BS****
0.068	17.5	12.0	6.0	15.0	0.6	C26Q2683-60****	1.0	32.0	20.0	11.0	27.5	0.8	C26Q2105-BS****
0.082	17.5	12.0	6.0	15.0	0.6	C26Q2823-60****	1.2	32.0	22.0	13.0	27.5	0.8	C26Q2125-BS****
0.10	17.5	12.0	6.0	15.0	0.6	C26Q2104-6S****	1.5M	32.0	22.0	13.0	27.5	0.8	C26Q2155MBS****
0.12	17.5	12.0	6.0	15.0	0.6	C26Q2124-6S****	1.5K	32.0	25.0	13.0	27.5	0.8	C26Q2155KBS****
0.15	17.5	13.5	7.5	15.0	0.6	C26Q2154-6S****	1.8	32.0	28.0	14.0	27.5	0.8	C26Q2185-BS****
0.18	17.5	13.5	7.5	15.0	0.6	C26Q2184-6S****	2.2	32.0	28.0	14.0	27.5	0.8	C26Q2225-BS****
0.22	17.5	14.5	8.5	15.0	0.6	C26Q2224-6S****	2.2M	32.0	24.5	15.0	27.5	0.8	C26Q2225MBA****
0.27	17.5	16.0	10.0	15.0	0.8	C26Q2274-6S****	1.0	41.0	22.0	11.0	37.5	1.0	C26Q2105-FS****
0.33	17.5	16.0	10.0	15.0	0.8	C26Q2334-6S****	1.2	41.0	22.0	11.0	37.5	1.0	C26Q2125-FS****
0.39M	17.5	16.0	10.0	15.0	0.8	C26Q2394M6S****	1.5	41.0	24.0	13.0	37.5	1.0	C26Q2155-FS****
0.39K	17.5	19.0	11.0	15.0	0.8	C26Q2394K6S****	1.8	41.0	24.0	13.0	37.5	1.0	C26Q2185-FS****
0.47M	17.5	19.0	11.0	15.0	0.8	C26Q2474M6S****	2.2	42.0	28.0	14.0	37.5	1.0	C26Q2225-FS****
							2.2	41.0	26.0	15.0	37.5	1.0	C26Q2225-FA****

Note: 1. "—" =capacitance tolerance code, M=±20%,K=±10%  
2. "\*\*\*\*" =lead form and packaging mode code (refer to table 1)

**■ Maximum permissible voltage change per unit of time**

Rated Voltage (Vac)	dV/dt(V/us) at 440 Vdc				
	P=10mm	P=15mm	P=22.5mm	P=27.5mm	P=37.5mm
305	100	90	50	35	25

Note:

1. Rated voltage pulse slope ( $dV/dt_R$ ) at rated voltage.
2. If the working voltage( $U$ ) is lower than the rated voltage( $U_R$ ), the capacitor can be worked at a higher  $dV/dt$ . In this case, the maximum allowed  $dV/dt$  is obtain by multiplying the right value with  $U_R/U$ .

**■ Test Method And Performance (IEC 60384-14)**

Group	Item	Conditions of test	Performance requirements
A1	4.1 Visual examination	Dimensions: gauging by vernier caliper	No visible damage & legible marking
	4.1Dimensions(Gauging)		Fit detail specification
A2	4.2.2 Capacitance	Measuring frequency: Capacitance: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz Voltage proof between terminals: 4.3UR(d.c.), 1min IR. test voltage: 100Vd.c.	Within specified tolerance
	4.2.3 Tangent of loss angle		No permanent breakdown or flashover
	4.2.1 Voltage proof		
	4.2.5 Insulation Resistance		I.R.:≥ the rated value
B1	4.5 Solderability	Methods: Groove welding Ta, Method 1 Solder temperature: 245°C±5°C Immersion time: 2.0s±0.5s	Good quality of tinning
C1A	Initial measurement	Dimensions: gauging by vernier caliper Measuring frequency: Capacitance: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz	No visible damage & legible marking
			Fit detail specification
			Within specified tolerance
	4.1.1 Creepage distances and Clearances	Gauging by vernier caliper	Creepage distances≥ 4.0mm Clearances≥ 3.0mm
	4.3 Robustness of Terminations (straight lead)	Tense: 0.50 < d ≤ 0.80, 10N 0.80 < d ≤ 1.25, 20N Ub bending test: Bend: 0.50 < d ≤ 0.80, 5N 0.80 < d ≤ 1.25, 10N The terminals shall be bent 2 times in each direction	No visible damage
	4.4 Resistance to Soldering heat	Capacitors are not pre-dried Groove Method Tb, Method 1A Solder temperature: 260°C±5°C Immersion time: 10s±1s	No visible damage & legible marking
	4.19 Component solvent resistance	Solvent: industrial isopropyl Solvent temperature: 23°C±5°C Dipping time: 5min±0.5min Method 2: (without Sassafras test) Recovery time: 48h	Comply with the specifications in the product size table
	Final measurement	Appearance inspection Cap. measuring frequency: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz	No visible damage Cap.:   ΔC   /C ≤ 5% Tangent of loss angle: CN≤ 1μF: ≤ 0.008 (10kHz) CN > 1μF: ≤ 0.005 (1kHz)

Group	Item	Conditions of test	Performance requirements
C1B	Initial measurement	4.1Visual examination 4.1Dimensions (Gauging) 4.2.2Capacitance 4.2.3Tangent of loss angle Dimensions: gauging by vernier caliper Measuring frequency: Capacitance: 1kHz Tangent of loss angle: $C_N \leq 1\mu F$ : 10kHz; $C_N > 1\mu F$ : 1kHz	No visible damage & legible marking Fit detail specification Within specified tolerance
	4.5 Solderability	Methods: Groove welding Ta, Method 1 Solder temperature: 245°C±5°C Immersion time: 2.0s±0.5s	Good quality of tinning
	4.20 Solvent resistance of the marking	Solvent: Industrial isopropanol. Solvent temperature: 23°C±5°C Dipping time: 5min±0.5min Condition: scrub Scrub material: absorbent cotton Reverting time: No	The marking shall be legible
	4.6 Rapid change of temperature	$T_A = -40^\circ C$ , $T_B = +105^\circ C$ 5 cycles, Duration: t=30min	No visible damage
	4.7 Vibration (straight lead) (when capacitor weight > 3g, the capacitor body needs to be fixed)	Amplitude 0.75mm or acceleration 98m/s <sup>2</sup> (whichever is the smaller severity), f: 10Hz to 500Hz.Three directions, 2h for each direction, total 6h.	No visible damage
	4.8 Bump (straight lead) (when capacitor weight > 3g, the capacitor body needs to be fixed)	4 000 times, Acceleration: 400m/s <sup>2</sup> , Pulse duration, 6ms	No visible damage
	Final measurement	Appearance inspection Cap. measuring frequency: 1kHz	No visible damage Cap.:   $\Delta C$   /C ≤ 5%
	Initial measurement	According to the conditions of Group C1A and C1B	According to the requirements of Group C1A and C1B
	Dry heat	+105°C, 16h	No visible damage & legible marking
C1	Damp heat, Cyclic	Test Db, Severity: b, the first cycle Temperature: +55°C, 24h each cycle, Method 2	
	Cold	-40°C, 2h	
	Damp heat, Cyclic	Test Db, Severity b, the other cycles Temperature: +55°C, 24h each cycle, Method 2	
	Final measurement	Measuring frequency: Capacitance: 1kHz Tangent of loss angle: $C_N \leq 1\mu F$ : 10kHz; $C_N > 1\mu F$ : 1kHz Voltage proof between terminals: 4.3U <sub>R</sub> (d.c.),1min Voltage proof between terminal and housing: 2U <sub>R</sub> +1500V(a.c.),1min Insulation resistance test voltage: 100Vd.c.	Cap.:   $\Delta C$   /C ≤ 5% Increase of tgδ: $C_N \leq 1\mu F$ : ≤ 0.008 (10kHz) $C_N > 1\mu F$ : ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: ≥ 50% of the rated value



Group	Item	Conditions of test	Performance requirements
C2	4.12 Damp heat, steady state	Temperature: 40°C ±2°C Humidity: 93±3%RH Duration: 56 days	No visible damage & legible marking Cap.:   $\Delta C$   /C ≤ 5% Increase of tgδ: C <sub>N</sub> ≤ 1μF: ≤ 0.008 (10kHz) C <sub>N</sub> > 1μF: ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: ≥ 50% of the rated value
	Final measurement	Tangent of loss angle: C <sub>N</sub> ≤ 1μF: 10kHz; C <sub>N</sub> > 1μF: 1kHz Voltage proof between terminals: 4.3U <sub>R</sub> (d.c.), 1min Voltage proof between terminal and housing: 2U <sub>R</sub> +1500V(a.c.), 1min Insulation resistance test voltage: 100Vd.c.	
C3	Initial measurement	Measuring frequency capacitance: 1kHz Tangent of loss angle: C <sub>N</sub> ≤ 1μF: 10kHz; C <sub>N</sub> > 1μF: 1kHz Insulation resistance test voltage: 100Vd.c.	Within specified tolerance
	4.13 Impulse voltage	Each individual capacitor shall be subjected to 24 impulses of the same polarity, the time between impulses shall not be less than 10S, and the peak value of the voltage impulse: 2.0kV (suitable for C <sub>N</sub> ≤ 1μF; When C <sub>N</sub> > 1μF, the capacitor can endure pulse voltage value is $2.0/\sqrt{C_N}$ kV)	There are three or more waveforms which indicate that no self-healing breakdown have occurred when it is monitored by the monitor (when any three successive impulses are shown by the monitor to have a wave form indicating that no self-healing breakdown have taken place the impulses can be stopped)
	4.14 Endurance	Temperature : +110°C Duration : 1000h Voltage: at 1.25 U <sub>R</sub>	No visible damage & legible marking Cap.:   $\Delta C$   /C ≤ 10% Increase of tgδ: C <sub>N</sub> ≤ 1μF: ≤ 0.008 (10kHz) C <sub>N</sub> > 1μF: ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: ≥ 50% of the rated value
	Final measurement	Tangent of loss angle: C <sub>N</sub> ≤ 1μF: 10kHz; C <sub>N</sub> > 1μF: 1kHz Voltage proof between terminals: 4.3U <sub>R</sub> (d.c.), 1min Voltage proof between terminal and housing: 2U <sub>R</sub> +1500V(a.c.), 1min	




Group	Item	Conditions of test	Performance requirements
C4	4.15 Charging and discharging	Times: 10 000 Duration of charging: 0.5s Duration of discharging: 0.5s Charging voltage: $\sqrt{2}U_R$ Vd.c. Charging resistance: $220/C_N(\Omega)$ or the current $\leq 1.0A$ (whichever is the minor) Discharging resistance: $R = \frac{\sqrt{2}U_R}{C_N \times \frac{dU}{dt}} (\Omega)$ $C_N$ : Capacitance ( $\mu F$ ) $dU/dt(V/\mu s)$ : $100V/\mu s$	Cap.: $ \Delta C /C \leq 10\%$ Increase of $\tan\delta$ : $C_N \leq 1\mu F$ : $\leq 0.008$ (10kHz) $C_N > 1\mu F$ : $\leq 0.005$ (1kHz) I.R.: $\geq 50\%$ of the rated value
C6	4.17 Passive flammability	Needle flame test The category of flammability: B Expose time: 1 time Capacitor Volume      Exposing time $250 < V(\text{mm}^3) \leq 500$ 20s $500 < V(\text{mm}^3) \leq 1750$ 30s $V(\text{mm}^3) > 1750$ 60s	The flaming time of each capacitor shall not go beyond 10s after it is taken apart from the flame. Drop of each capacitor caused by flame shall not fire the tissue below.
C7	4.18 Active flammability	The specimens shall be individually wrapped in at least 1, but not more than 2, complete layers of cheesecloth, the cheesecloth shall be untreated pure cotton cloth. Each sample shall be subjected to 20 discharged, the interval between successive discharges shall be 5s. $U_i = 2.0kV_0^{+7} \%$ $U_R$ be applied and be maintained for $120_0^{+10}$ s after the last discharge.	The cheese cloth around the capacitor shall not burn with a flame.

**■ Marking (For example)**

◀▶ MKT61 305~ X2  
104K 40/105/56/B  
   


**Marking Introduction**

Sign	explain	Sign	explain
◀▶	Brand	40/105/56/B	Climate category / Passive Flammability Class
MKT61	Type		ENEC-SEMKO Approval
305~	Rated voltage		CQC Approval
X2	Class		UL,CUL Approval
104K	Rated capacitance and tolerance		

**■ Taping specification for box-type capacitors**
**▲ Outline Drawing**

**▲ Taping Dimensions(mm)**

Technology index title	Code	Dimensions				
		P=5.0	P=7.5	P=10.0	P=15.0	Tolerance
Taping type	—	Fig 1	Fig 1	Fig2	Fig 2	—
Part number	Ammo-Digit12-15	A201	A301	A405	A605	
Taping pitch	P <sub>3</sub>	12.7	12.7	25.4	25.4	±1.0
Feed hole pitch	P <sub>0</sub>	12.7	12.7	12.7	12.7	±0.3
Center of wire	P <sub>1</sub>	3.85	2.6	7.7	5.2	±0.7
Center of body	P <sub>2</sub>	6.35	6.35	12.7	12.7	±1.3
Pitch of taping wire	F**	5.0	7.5	10.0	15.0	+0.6 -0.1
Component alignment	△ S	0	0	0	0	±2.0
Height of component from tape center	H***	18.5	18.5	18.5	18.5	±0.5
Carrier tape width	W	18.0	18.0	18.0	18.0	+1.0 -0.5
Hold down tape width	W <sub>0</sub>	6min	10min	10min	10min	—
Hole position	W <sub>1</sub>	9.0	9.0	9.0	9.0	±0.5
Hold down tape position	W <sub>2</sub>	3max	3max	3max	3max	—
Feed hole dia.	D <sub>0</sub>	4.0	4.0	4.0	4.0	±0.2
Tape thickness	t	0.7	0.7	0.7	0.7	±0.2

**Note:** \* P<sub>0</sub>=15mm is also available;

\*\*F can be other lead spacing;

\*\*\*H=16.5mm is available;

## ■ Soldering suggestions


### ▲ Manual soldering

Max. temperature: 350°C, time: 3s


### ▲ Wave soldering

There are many factors affecting the heating of film capacitor during the wave soldering process, such as: preheating temperature, preheating time, soldering temperature, soldering time, other heat sources influence and so on.

The typical soldering profile is as below:



▲ Because overheating could damage the capacitor, we recommend paying attention to the maximum capacitor temperature and heating time, use temperature sensor to detect the maximum capacitor body temperature.




Note: If re-working or dipping twice is necessary, it should be done after the capacitor returns to the normal temperature.


Temperature sensor position (Tcapacitor body)	The capacitor body surface of lead side, capacitor height position from PCB: $h1=2\sim3mm$		
Maximum capacitor body temperature $Tp(^{\circ}C)$	OPP film $P \leq 15mm$	OPP film $P > 15mm$	PET film
	115	120	125
Maximum capacitor lead wire temperature( $^{\circ}C$ )	265	265	265
Maximum capacitor body heating time $tp=Tp-5^{\circ}C$	30s		

## ■ Packing box sizes(mm)(example)


1. Out packing box for bulk



2. Inner packing box for bulk



3. Box sizes for Ammo-pack



## ■ Storage conditions

▲ It must be noted that the solderability of the terminals may be deteriorated when stored in an atmosphere filled with moisture, dust, or a reactive oxidizing gas.(hydrogen chloride, hydrogen sulfide, sulfuric acid,etc.)

▲ It shouldn't be located in particularly high temperature and high humidity, it must submit to the following conditions(unchanging primal package):

Temperature: -40 °C to 35 °C

Humidity: Average per year≤ 70%RH;

For 30 full days randomly distributed throughout the year≤ 80%RH

Storage time for tinned lead wire: (from the date marked on the capacitor's body or the label glued to the package) :

Bulk(packed with plastic bag): ≤ 24 months ;

Taping and line up: ≤ 12 months