


1. External Dimensions (Unit:m/m)



TYPE	A	B	C	D	E	Q'Ty/ package
ADP15S19	16.5Max	20.0Max	5.0±1.0	0.8±0.1	7.5±0.5	/

2. Part Number Code

ADP 15 S 19 M 220 - 5MM
A B C D E F G

A: Series Name Choke Coils
 B: Dimensions(mm) 15: 16.5 Max
 C: Materials Shielded
 D: Thickness(mm) 19: 20.0Max
 E: Tolerance M: ±20%
 F: Inductance 220=22uH
 G: C Dimensions 5MM

3. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Test Frequency (Hz)	DCR(Max) (mΩ)	Heat Rating Current Irms(A)	Saturation Current Isat(A)
ADP15S19M220-5MM	22.0	±20%	1K/0.25V	25.0	8.0	5.0

4. Material List

NO	ITEM	SPECIFICATIONS	SUPPLIER	UL FILE
1	Core	DR2W11*13.5 B8.2	HC OR EQUIVALENT	N/A
		H50 P15.6*19*13	HC OR EQUIVALENT	N/A
2	Wire	2UEWF Φ 0.8*11.5Ts Ref	FR OR EQUIVALENT	E196072
3	UL	Φ 12mm Black	CY OR EQUIVALENT	E180908
4	Tin	HB07H	CD OR EQUIVALENT	N/A
5	Epoxy	E-506	LD OR EQUIVALENT	N/A