






FOR SWS



3 TE LOGO

2386053-4	A	CuZn30	Sn	1.0mm ²	1.9-2.1	G=3.6 H=3.69 N=2.25	E=2.78 F=2.62 J=1.3	A=6.0 B=3.0 C=2.0 D=0.2 L=11.4 M=0.6	UNSEAL
2386053-3	A			0.75mm ²	1.7-1.9	G=2.8 H=2.92 N=1.6	E=2.52 F=2.44 J=1.1	A=5.8 B=3.0 C=1.8 D=0.2 L=11.4 M=0.6	
2386053-2	A			0.5mm ²	1.4-1.6	G=2.8 H=2.92 N=1.6	E=2.15 F=1.99 J=1.0	A=5.6 B=2.8 C=1.8 D=0.2 L=11.4 M=0.6	
2386053-1	A			0.35mm ²	1.2-1.4	G=2.35 H=2.47 N=1.3	E=1.9 F=1.82 J=0.29	A=5.6 B=2.5 C=2.0 D=0.2 L=11.4 M=0.6	
2377789-4	A	CuZn30	Sn	1.0mm ²	1.9-2.1	G=4.27 H=4.1 N=2.9	E=2.78 F=2.62 J=1.3	A=6.8 B=3.0 C=2.0 D=0.8 L=12.2 M=0	SWS
2377789-3	A			0.75mm ²	1.7-1.9	G=4.31 H=4.08 N=2.6	E=2.52 F=2.44 J=1.1	A=6.8 B=3.0 C=2.0 D=0.8 L=12.2 M=0	
2377789-2	A			0.5mm ²	1.4-1.6	G=4.12 H=3.84 N=2.6	E=2.15 F=1.99 J=1.0	A=6.6 B=2.8 C=2.0 D=0.8 L=12.2 M=0	
2377789-1	A			0.35mm ²	1.2-1.4	G=4.19 H=3.84 N=2.6	E=1.97 F=1.82 J=0.13	A=6.4 B=2.6 C=2.0 D=0.8 L=12.2 M=0	
P/N	REV.	MATERIAL	PLATING	WIRE RANGE	INSULATION-φ	INS CRIMP mm	WIRE CRIMP mm	LENGTH mm	SWS/UNSEAL