


Notice:This fastener is a part of the total design and its use in the completed assembly is controlled by the user. Stanley assumes responsibility only for meeting specifications shown on this drawing

Stanley will supply parts per this drawing. If in agreement, please sign & return promptly.  
Auhtorized by:

\_\_\_\_\_  
(Title)  
\_\_\_\_\_  
(Date)

Rev.	Revisions/E.C. number / change	Date	By
01	NEW RELEASE	14-Nov-24	Kaichao



NOTES:

1. MATERIAL:LOW CARBON STEEL,SWRCH18A AND EQUIVALENT.
2. HEAT TREATMENT:CASE HARDEN  
CORE HARDNESS:250-400HV  
CASE HARDNESS:400-550HV
3. FINISH:BLACK NICKEL PLATING, COATING CANNOT BE PEELED OFF
4. PARTS SHALL BE PASSED 4 HOURS SST W/O RED RUST
5. BROKEN TORQUE:MIN 13.0KGF.CM
6. PARTS ARE TO BE CLEAN AND FREE FROM FOREIGN MATERIAL. DIRT,OIL,GREASE,MOLD RELEASE OR OTHER CONTAMINANTS ARE NOT ALLOWED.
7. THE PART MUST COMPLY WITH RoHS REQUIREMENT.

DIMENSIONS ARE IN MILLIMETER  
TOLERANCES  
0-6 ±0.10  
6-30 ±0.20  
30-120 ±0.30  
ANGLES ±1.0°  
DO NOT SCALE DRAWINGS

Customer Name:		<div>STANLEY Engineered Fastening</div>	Unit : Metric	Drawing No. : HPLC-S30CS-0003	
Customer Part No.: C357398	Revision: 01			Drawn By: Kaichao Li	Date: 14-Nov-24
Description: 圆头十字机牙螺栓螺钉螺丝, PM3X5, 镍			Size: A4	Checked By: Jay Lu	Date: 14-Nov-24
This drawing is the property of and may embody proprietary information owned by Stanley. It is provided under confidential relationship for a specific purpose and to return it to Stanley upon request. Copyright © Stanley . All right reserved.			Dimensions & tolerances as per ISO 2768	DO NOT SCALE	Approved By: