




| REV. | EC# | DESCRIPTION | DATE      | DRAWN | CHECK | APPROVED |
|------|-----|-------------|-----------|-------|-------|----------|
| 1.00 |     | 初版发行        | 2020-8-28 |       |       |          |
|      |     |             |           |       |       |          |
|      |     |             |           |       |       |          |

|                |       |       |       |       |
|----------------|-------|-------|-------|-------|
| 15P            | 32.0  | 28.0  | 30.9  | 26.8  |
| 14P            | 30.0  | 26.0  | 28.9  | 24.8  |
| 13P            | 28.0  | 24.0  | 26.9  | 22.8  |
| 12P            | 26.0  | 22.0  | 24.9  | 20.8  |
| 11P            | 24.0  | 20.0  | 22.9  | 18.8  |
| 10P            | 22.0  | 18.0  | 20.9  | 16.8  |
| 9P             | 20.0  | 16.0  | 18.9  | 14.8  |
| 8P             | 18.0  | 14.0  | 16.9  | 12.8  |
| 7P             | 16.0  | 12.0  | 14.9  | 10.8  |
| 6P             | 14.0  | 10.0  | 12.9  | 8.8   |
| 5P             | 12.0  | 8.0   | 10.9  | 6.8   |
| 4P             | 10.0  | 6.0   | 8.9   | 4.8   |
| 3P             | 8.0   | 4.0   | 6.9   | 2.8   |
| 2P             | 6.0   | 2.0   | 4.9   | 0.8   |
| NUMBER OF PINS | DIM.A | DIM.B | DIM.C | DIM.D |



技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

适应基板厚度：1.2mm~1.6mm

温度范围:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$

额定电压: 250V AC/DC

额定电流: 2A

绝缘电阻:  $\geq 100\text{M}\Omega$

耐 压: 800V AC/minute

|     |         |       |                         |
|-----|---------|-------|-------------------------|
| 2   | PIN     | n PCS | 材质:黄铜,电镀:镀亮锡60u"MIN     |
| 1   | Housing | 1 PCS | 材质:PA66 (UL94V-0),颜色:白色 |
| NO. | NAME    | Q'TY  | DESCRIPTION             |



® 深圳市韩下电子有限公司

|                  |     |           |                     |           |               |        |                                                                                       |
|------------------|-----|-----------|---------------------|-----------|---------------|--------|---------------------------------------------------------------------------------------|
| DRAW :           | 黄彬  | 2020-8-28 | TITLE:              |           | DRAW NAME:    |        |                                                                                       |
| DESIGN:          |     |           | 插件针座                |           | HX-PH2.0-5PWZ |        |                                                                                       |
| CHECK:           | 张伟  | 2020-8-28 | SERIES: 1501 SERIES |           | DRAW NO.      |        |                                                                                       |
| APPROVED         | 罗小春 | 2020-8-28 | P/N:                |           | UNIT:         | SHEET: |  |
| CUSTOMER DRAWING |     |           | REV. 1.00           | SCALE N/A | mm            | 1/1    |                                                                                       |

| GENERAL TOLERANCES |       |        |        |
|--------------------|-------|--------|--------|
| DIM                | TOL   | DIM    | DEG    |
| X.                 |       | X°     | ±3.00° |
| X.X                | ±0.35 | X.X°   | ±2.00° |
| X.XX               | ±0.25 | X.XX°  | ±1.00° |
| X.XXX              | ±0.15 | X.XXX° |        |

Technical drawing of a shaft with five holes. The distance between the first and last hole is DIM.B. The hole diameter is  $\varnothing 0.70$  with a tolerance of  $+0.10/0$ .

## PCB LAYOUT