

Features



- N-Channel, 5V Logic Level Control
- Enhancement mode
- Very low on-resistance $R_{DS(on)}$ @ $V_{GS}=4.5\text{ V}$
- Fast Switching
- 100% Avalanche test
- Pb-free lead plating; RoHS compliant



Halogen-Free

Part ID	Package Type	Marking	Packing
VS3618AP	PDFN5x6	3618AP	3000PCS/Reel

PDFN5x6



Maximum ratings, at $T_A=25^\circ\text{C}$, unless otherwise specified

Symbol	Parameter		Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage		30	V
V_{GS}	Gate-Source voltage		± 20	V
I_S	Diode continuous forward current	$T_C=25^\circ\text{C}$	54	A
I_D	Continuous drain current @ $V_{GS}=10\text{V}$	$T_C=25^\circ\text{C}$	54	A
		$T_C=100^\circ\text{C}$	34	A
I_{DM}	Pulse drain current tested ①	$T_C=25^\circ\text{C}$	216	A
I_{DSM}	Continuous drain current @ $V_{GS}=10\text{V}$	$T_A=25^\circ\text{C}$	20	A
		$T_A=70^\circ\text{C}$	16	A
EAS	Avalanche energy, single pulsed ②		25	mJ
P_D	Maximum power dissipation	$T_C=25^\circ\text{C}$	32	W
P_{DSM}	Maximum power dissipation ③	$T_A=25^\circ\text{C}$	4.2	W
T_{STG}, T_J	Storage and junction temperature range		-55 to 150	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	3.9	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	30	$^\circ\text{C/W}$

Electrical Characteristics

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
Static Electrical Characteristics @ T _j =25°C (unless otherwise stated)						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	30	—	—	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =30V, V _{GS} =0V	—	—	0.1	μA
	Zero Gate Voltage Drain Current(T _j =125°C)	V _{DS} =30V, V _{GS} =0V	—	—	100	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V	—	—	±100	nA
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	1.3	1.8	2.4	V
R _{DS(ON)}	Drain-Source On-State Resistance ④	V _{GS} =10V, I _D =20A	—	5.4	8	mΩ
		T _j =100°C	—	7.3	—	mΩ
R _{DS(ON)}	Drain-Source On-State Resistance ④	V _{GS} =4.5V, I _D =15A	—	8.4	11	mΩ
Dynamic Electrical Characteristics @ T _j = 25°C (unless otherwise stated)						
C _{iss}	Input Capacitance	V _{DS} =15V, V _{GS} =0V, f=1MHz	940	1110	1280	pF
C _{oss}	Output Capacitance		150	180	210	pF
C _{rss}	Reverse Transfer Capacitance		110	130	150	pF
R _g	Gate Resistance	f=1MHz	—	1.9	—	Ω
Q _g (10V)	Total Gate Charge	V _{DS} =15V, I _D =15A, V _{GS} =10V	17	23	30	nC
Q _g (4.5V)	Total Gate Charge		7	12	20	nC
Q _{gs}	Gate-Source Charge		2	4.2	10	nC
Q _{gd}	Gate-Drain Charge		2	4.9	11	nC
Switching Characteristics						
t _{d(on)}	Turn-on Delay Time	V _{DD} =15V, I _D =15A, R _G =6.8Ω, V _{GS} =10V	—	14	—	ns
t _r	Turn-on Rise Time		—	27	—	ns
t _{d(off)}	Turn-Off Delay Time		—	65	—	ns
t _f	Turn-Off Fall Time		—	19	—	ns
Source- Drain Diode Characteristics@ T _j = 25°C (unless otherwise stated)						
V _{SD}	Forward on voltage	I _{SD} =20A, V _{GS} =0V	--	0.85	1.2	V
t _{rr}	Reverse Recovery Time	T _j =25°C, I _{sd} =15A, V _{GS} =0V	—	31	—	ns
Q _{rr}	Reverse Recovery Charge	di/dt=100A/μs	—	95	—	nC

NOTE: ① Repetitive rating; pulse width limited by max junction temperature.

② Limited by T_{jmax} , starting $T_j = 25^{\circ}\text{C}$, $L = 0.5\text{mH}$, $R_G = 25\Omega$, $I_{AS} = 10A$, $V_{GS} = 10V$. Part not recommended for use above this value

③ The power dissipation P_{DSM} is based on $R_{\theta JA}$ and the maximum allowed junction temperature of 150°C .

④ Pulse width $\leq 380\mu s$; duty cycles $\leq 2\%$.

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. $V_{GS(TH)}$ Gate-Source Voltage Vs. T_J




Fig3. Typical Transfer Characteristics




Fig4. Normalized On-Resistance Vs. T_J




Fig5. Typical Source-Drain Diode Forward Voltage










Fig6. Maximum Safe Operating Area

Typical Characteristics


Fig7. Typical Capacitance Vs.Drain-Source Voltage

Fig8. Typical Gate Charge Vs.Gate-Source Voltage

Fig9. Normalized Maximum Transient Thermal Impedance

Fig10. Unclamped Inductive Test Circuit and waveforms

Fig11. Switching Time Test Circuit and waveforms

Marking Information



1st line: Vergiga Code (Vs), Vergiga Logo

2nd line: Part Number (3618AP)


3rd line: Date code (XXXYWW)

XXX: Wafer Lot Number Code, code changed with Lot Number

Y: Year Code, refer to table below

WW: Week Code (01 to 53)

Code	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T
Year	2015	2016	2017	2018	2019	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030

PDFN5x6 Package Outline Data


Symbol	DIMENSIONS (unit : mm)		
	Min	Typ	Max
A	0.90	1.00	1.20
A1	0.00	--	0.05
b	0.30	0.40	0.51
c	0.20	0.25	0.33
D	4.80	4.90	5.40
D1	3.61	4.00	4.25
E	5.65	5.80	6.06
E1	5.90	6.10	6.35
E2	3.38	3.58	3.92
e	1.27 BSC		
L	0.51	0.61	0.71
L1	--	--	0.15
L2	0.41	0.51	0.61
θ	0°	--	12°

Notes:

1. Refer to JEDEC MO-240 variation AA.
2. Dimensions "D" and "E" do NOT include mold flash protrusions or gate burrs.
3. Dimensions "D" and "E" include interterminal flash or protrusion. Interterminal flash or protrusion shall not exceed 0.25mm per side.

Customer Service
Sales and Service:
sales@vgsemi.com
Vergiga Semiconductor CO., LTD
TEL: (86-755) -26902410

FAX: (86-755) -26907027

WEB: www.vgsemi.com