



1. Compatible with various 10/100 Base-TX transceiver requiring 1:1 transmit and receive turns ratio
2. Compliant with IEEE 802.3at standard including baseline wander compensation specification of $350\mu\text{H}$ OCL when Biased at 8mA
3. Low profile Surface Mount Packaging designed for Hi-Temp Reflow Process
4. Single channel interface for 10/100Mbps Ethernet applications with CMC's tuned to Enhance EMC system performance
5. Operating Temperature range: -40°C TO $+85^{\circ}\text{C}$
6. Storage temperature range: -40°C TO $+125^{\circ}\text{C}$



DIMENSIONS & SCHEMATICS




Note: 1. Dimension: mm, 2. Unless otherwise specified, tolerances are: ± 0.15 mm



TECHNICAL SPECIFICATIONS

OCL :	$350\mu\text{H}$ Min. @ 100 KHz, 100mV with 8mA DC Bias
Leakage	$0.5\mu\text{H}$ Max. @ 100KHz, 0.1V
Inductance: Cw/w:	28pF Max. @ 100KHz, 0.1V
DCR:	1.20Ω Max.
Turns Ratio($\pm 2\%$):	1CT:1CT(TX), 1CT:1CT(RX)
Polarity:	1-16, 6-11 In-Phase
Insertion Loss:	-1.1 dB Max. @ 1-100MHz
Return Loss:	-20dB Min. @ 1-30MHz -14 dB Min. @ 30-60 MHz -11.5 dB Min. @ 60-80 MHz
Cross Talk:	-45 dB Min. @ 30 MHz -40 dB Min. @ 60 MHz -35dB Min. @ 80 MHz
Common Mode Rejection :	-42 dB Min. @ 1-30 MHz -37 dB Min. @ 50 MHz -33 dB Min. @ 100 MHz
Isolation HI-POT:	1500Vrms 1mA 1Second

PACKING SPECIFICATION



1. units/reel: 600PCS
2. reel/carton: 7PCS
3. units/carton : 4200PCS

EXPORT CARTON: 367(L)x337(W)x235(H)