








RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.05)

NOTES :

1.0. RATING :

1.1. VOLTAGE :60 VAC (R.M.S.)

1.2. NOMINAL CHARACTERISTIC IMPEDANCE: 50 Ohm

1.3. APPLICABLE FREQUENCY: DC ~ 6GHz

1.4. VSWR: 1.3 MAX. (DC~3GHz), 1.5 MAX. (3~6GHz)

1.5. TEMPERATURE :−40°C TO +85°C

2.0. ALL DIMENSIONS SHOULD BE CONTROLLED IN FAI.:

3.0. MARKED ∇^* SHOULD BE CONTROLLED BY QIP.:

4.0. MATERIAL SEE BILL OF MATERIAL :

		new		2015/5/3		A		瀚源		
ECN BO.		DESCRIPTION.		DATE.		REV.				
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1		
Mikey	Tom	Jerry	PART NAME	IPEX-4		UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	IPEX-4		SPECIFIED,TOLERANCE:		X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15		
					ANGULAR ±3°				FILE.NO.	