


1. Designed for long haul 2.5G Single Port Transformer Module
2. Supports four pairs of category 5 UTP cable,Cable interface for isolation and low common mode emissions.
- 3 . Low profile Surface Mount Packaging designed for Hi-Temp Reflow Process
4. Compliant with IEEE 802.3bz standard for 2.5G Base-Z,Designed to support 1:1 Turns Ratio Transceivers.



DIMENSIONS & SCHEMATICS




Note: 1、 Dimension: mm; 2.Unless otherwise specified,tolerances are: ± 0.15mm

TECHNICAL SPECIFICATIONS

OCL :	150 μ H Min. @ 100 KHz, 100mV with 8mA DC Bias
Leakage Inductance:	0.5 μ H Max. @ 100KHz, 0.1V
Cw/w:	35 pF Max. @ 100KHz, 0.1V
DCR:	1.20 Ω Max
Turns Ratio($\pm$ 5%):	1CT:1(TX), 1CT:1(RX)
Polarity:	1-24, 4-21, 8-17, 11-14In-Phase
Insertion Loss:	-1.0 dB Max. @ 1-125MHz -2.0dB Max. @ 100-250MHz
Return Loss:	-16 dB Min. @ 1-40MHz -16+10*log(f/40)dB Min. @ 40-100MHz -12dB Min. @ 100.1-200MHz
Cross Talk:	-35dB Min.@ 1-100 MHz -25dB Min.@ 100-200 MHz
Common Mode Rejection :	-25dB Min.@30-200 MHz
Isolation HI-POT:	1500Vrms
Operating Temperature range:	-40 $^{\circ}$ C ~ + 85 $^{\circ}$ C
Storage temperature range:	-40 $^{\circ}$ C ~ + 125 $^{\circ}$ C

PACKING SPECIFICATION



1. units/reel:32PCS
2. reel/carton:90PCS
- 3.units/carton :2880PCS