



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PP BLACK

b.TERMINAL(-):BRASS

c.TERMINAL(+):BRASS

(SURFACE PLATING: Brass natural color)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 270V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-2032-B1AW003-100

电池盒

电池型号

SMT 180° TYPE

线长(MM)

PLATING:

A-Au1U"

J-Ni-PLATING

K-Sn-PLATING

W-无镀层 本色

MATERIAL:

1A-PP BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK


4A-LCP WHITE

4B-LCP BLACK

工程部

2023-12-08

H. WANG



3	TERMINAL(+)	1	BRASS, T=0.15MM	Brass natural color
2	TERMINAL(-)	1	BRASS, T=0.15MM	Brass natural color
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2023-12-08	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2023-12-08	电池盒BH-2032-1J(26#红黑线长100mm剥皮上锡5mm无开关)	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2023-12-08	PART NO.:	
X.XX :±0.20		WEIGHT:		SCALE:	SIZE: A4	VIEW:	BH-2032-B1AW003-100
X.XXX :±0.10		SHEET 1 OF 1		UNIT: mm	REV.: A/1	OBJECT: MY	DRAW NO.:WD-CP-0363