

注: 未经许可禁止传播、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2.Torque value: M2.0, 1.77Lb.in

3.Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

2. Torque value: M2, 0.2Nm

3.wire range: 0.2~1.5mm²

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Cover: PA66 (UL94V-0)

3.Cage: Brass (Ni Plated)

4.Conductor: Copper alloy (Sn Plated)

5.Screw: Steel (M2.0,Zn Plated)

NOTES3:

1.Pitch: 3.81mm Poles: 02-24P





2.Stripping length: 7-8mm

3.Operating temperature: -40℃~+105℃

4.RoHS Compliance

How to order

MX15EDGRKF	-	3.81	-	XXP	-	XXXX	-	XX	-	X	-	X
产品型号		间距		极数		颜色:						A-Z其他定制
						灰色:GY	橙色:OE	01:常规颜色				0:Y-字螺丝
						蓝色:BU	红色:RD	02-99:				1:S十字螺丝
						黑色:BK	透明色:TT	定制颜色				2:P平头十字螺丝
						绿色:GN	黄色:YW					Cu:铜方块
						白色:WE						Fe:铁方块



Pitch Range In mm			Nominal Dimension Range In mm					—	∩	□
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	24.03.13	UNITS	MM	SHEET/OF	1/1	A
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE						
	CIXI MAIXU ELECTRONICS CO.,LTD.							
	慈溪市迈旭电子有限公司							
	MX15EDGRKF-3.81-XXP							
	DWGNO.							