


承認書

SPECIFICATION FOR APPROVAL

NO: CMT20101012



PRODUCTION CORD

CMT20101012

性能測試數據

Core Factor	0.906mm ⁻¹
-------------	-----------------------

Le (mm ⁻¹)	43.56
------------------------	-------

Ae (mm ²)	48
-----------------------	----

Ve (mm ³)	2092.5
-----------------------	--------

DIMENSION 尺寸			MATERIAL 材料			TESTING CONDITION 測試條件	CUSTOMER 客戶名稱
Measuring unit: mm			NT2			測試儀器: TH2826A	
OD	20.00	±0.5	初始磁導率	10K (100KHZ)	14K (10KHZ)	T=25℃ 1000V 1mA 3sec 1TS	
ID	10.00	±0.5	比損耗因子	<8x10 ⁻⁶		10KHz	AL:>12uH 1KHz/0.25V 100Ω
HT	10.00	±0.3	飽和磁通密度	≥240 (80℃)	≥380 (25℃)	DATE: 2025/4/1	