











RECOMMENDED FPC



Detail B
Scale 4:1



RECOMMENDED PCB MOUNTING PATTERN

Note:

1. Material:

1.1 Housing: thermoplastic high temp.UL94V-0;

1.2 Latch: thermoplastic high temp.UL94V-0;

1.3 Terminal: copper alloy.

1.4 Fitting Nail: copper alloy.

2. Finish:

2.1 Terminal:

50~100u" Nickel under plating over all

!Gold flash on contact and solder area.

K:3u" Gold on contact and Gold Flash on Solder

M:5u" Gold on contact and Gold Flash on Solder

2.2 Fitting Nail:

50~100u" Nickel under plating over all

80~150u" Matte tin over all

3. Product must comply HF RoHS specification.

4. Product No: 5001-FCB 03 09 -** R 1-00

ALTERNATE

PACKING :R:卷

PIN

HIGH:0.9

PITCH:0.3

JME CONNECTOR SERIES

CKTS	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
9	4.30	1.80	2.40	3.03	3.73	3.00
11	4.90	2.40	3.00	3.63	4.33	3.60
13	5.50	3.00	3.60	4.23	4.93	4.20
15	6.10	3.60	4.20	4.83	5.53	4.80
17	6.70	4.20	4.80	5.43	6.13	5.40
19	7.30	4.80	5.40	6.03	6.73	6.00
21	7.90	5.40	6.00	6.63	7.33	6.60
23	8.50	6.00	6.60	7.23	7.93	7.20
25	9.10	6.60	7.20	7.83	8.53	7.80
27	9.70	7.20	7.80	8.43	9.13	8.40
29	10.30	7.80	8.40	9.03	9.73	9.00
31	10.90	8.40	9.00	9.63	10.33	9.60
33	11.50	9.00	9.60	10.23	10.93	10.20
35	12.10	9.60	10.20	10.83	11.53	10.80
37	12.70	10.20	10.80	11.43	12.13	11.40
39	13.30	10.80	11.40	12.03	12.73	12.00
41	13.90	11.40	12.00	12.63	13.33	12.60
43	14.50	12.00	12.60	13.23	13.93	13.20
45	15.10	12.60	13.20	13.83	14.53	13.80
47	15.70	13.20	13.80	14.43	15.13	14.40
49	16.30	13.80	14.40	15.03	15.73	15.00
51	16.90	14.40	15.00	15.63	16.33	15.60
53	17.50	15.00	15.60	16.23	16.93	16.20
55	18.10	15.60	16.20	16.83	17.53	16.80
57	18.70	16.20	16.80	17.43	18.13	17.40
59	19.30	16.80	17.40	18.03	18.73	18.00
61	19.90	17.40	18.00	18.63	19.33	18.60
63	20.50	18.00	18.60	19.23	19.93	19.20
65	21.10	18.60	19.20	19.83	20.53	19.80
67	21.70	19.20	19.80	20.43	21.13	20.40
69	22.30	19.80	20.40	21.03	21.73	21.00
71	22.90	20.40	21.00	21.63	22.33	21.60

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.15 0° ±5°	Unit(单位): MM
0.00 ±0.10 0° 0° ±3°	Scale(比例): 1:1
0.000 ±0.05 0° 0° ±1°	Page(页数): 1 OF 1
Project View (投影视角)	Rev(版本): A

深圳市文章济美科技有限公司

Shenzhen wenzhangjimei technology co., LTD

Product Name(产品名称):

0.3Pitch H=0.9 FPC/FFC Back-Flip RA Type1 SMT CONN

Product No(产品料号):

5001-FCB0309-**-R1-00

Designer(设计):

Checked(审核):

Approved(核准):

A	初版发行	2020/03/07	张孝雄
Rev	Change Description	Date	Revisor
版本	变更内容	日期	制/修订人