


注: 未经许可禁止传播、复制、编辑该文档, 以及利用其内容进行交流



Pitch Range In mm			Nominal Dimension Range In mm					—	∩	□
TO	Over	Over	TO	Over	Over	Over	TO	TO	TO	TO
6	6	10	30	30	60	100	150	0.1	10	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2.Torque value: M2.0, 1.77Lb.in

3.Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

2. Torque value: M2, 0.2Nm

3.wire range: 0.2~1.5mm²

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Cover: PA66 (UL94V-0)

3.Cage: Brass (Ni Plated)

4.Conductor: Copper alloy (Sn Plated)

5.Screw: Steel (M2.0,Zn Plated)

5.Nut: Brass

NOTES3:

1.Pitch: 3.81mm Poles: 02~24P

2.Stripping length: 7~8mm

3.Operating temperature: -40℃~+105℃

4.RoHS Compliance

How to order

MX15EDGRKP - 3.81 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 极数 01:常规颜色 0:Y一字螺丝

灰色:GY 橙色:OE 02~99: 定制颜色 1:S十字螺丝

蓝色:BU 红色:RD 定制颜色 Cu:铜方块 2:PS平头十字螺丝

黑色:BK 透明色:TT Fe:铁方块

绿色:GN 黄色:YW

白色:WE

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	24.03.13	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1 : 1	A4		
APP.		DATE		NAME	MX15EDGRKP-3.81-XXP			
 CIXI MAIXU ELECTRONICS CO.,LTD. 慈溪市迈旭电子有限公司								
DWGNO.								