



技术要求 Specification:

- 1、材质 Material: 黄铜 brass, 厚度 Thickness: $1.5 \pm 0.05\text{mm}$;
 - 2、表面处理 Surface treatment: 电镀锡 Electroplated tin;
 - 3、未注公差 Undeclared tolerance: $\pm 0.1\text{mm}$;
 - 4、符合RoHS环保要求 Complies with RoHS environmental requirements, 盐雾时间48H , with a salt spray time of 48 hours;
 - 5、包装方式 Packaging method: 载带包装 Carrier packaging.
 - 6、焊锡要求 Solder requirements: $260^\circ\text{C} \pm 10^\circ\text{C}$

未注尺寸公差 Unmarked dimensional tolerance standards:

线性 Linear:	
0.5~3	± 0.1
>3~6	± 0.15
>6~30	± 0.2
>30~120	± 0.3
>120~400	± 0.5
>400~1000	± 0.8
角度 angle:	$\pm 5^\circ$

标记	更改前	更改后	日期		材料		品名	STEIPU 深圳市斯泰普科技有限公司 Shenzhen STEIPU S&T Co.,Ltd.			
①					料 厚		SMT铜片	Part No.: STHW4-DU-HS160315			
②					比 例	1:1					
③					单 位	mm	制 图	石玉林	2024-6-5	图 幅 A4	
④					视 角		校 对				
							审 核				