







REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:PA10T
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING: Au-PLATING)
SEE ORDERING INFORMATION
2.ELECTRIC:
a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -40℃~+105℃

ORDERING INFORMATION
BS-10-B5BA011

电池座系列
BS-10系列
SMT 180° TYPE
PLATING:
A-Au-PLATING
J-Ni-PLATING
K-Sn-PLATING
MATERIAL:
5B-PA10T BLACK



PCB Layout Diagram
Top View

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Au-PLATING
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Au-PLATING
1	HOUSING	1	PA10T	BLACK

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2025-04-11
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-04-11
X.X :±0.25	X.X :±0.5°	APVD	XueShunyang	DATE	2025-04-11
X.XX :±0.20		WEIGHT:	SCALE: 1:1	SIZE: A4	VIEW: ④ ③
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE:	
				BS-2032-10-1 Au SMT PA10T	
				PART NO.:	
				BS-10-B5BA011	
				DRAW NO.:WD-CP-0461	