

Features

- Low operating voltage: 2.5V
- Ultra low capacitance: 2pF typical (I/O to I/O)
- Ultra low leakage: nA level
- Low clamping voltage
- -IEC 61000-4-2 (ESD) immunity test
 Air discharge: $\pm 30\text{kV}$
 Contact discharge: $\pm 30\text{kV}$
- -IEC61000-4-4 (EFT) 40A (5/50ns)
- -IEC61000-4-5(Lightning):100A(8/20 μs)
- These are Pb-Free Devices
- Response Time is Typically < 1 ns


Mechanical Characteristics

- Package: SOP-8
- UL 497B listed
- Case Material: "Green" Molding Compound
- Molding compound flammability rating:UL94V-0
- Packaging:Tube or Tape and Reel per EIA 481

Applications

- T1/E1 Line Cards
- T3/E3 and DS3 Interfaces
- STS-1 Interfaces
- 10/100 Ethernet

Schematic and Pin Configuration



Absolute Maximum Ratings(T_{amb}=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	P _{pp}	1000	W
Peak Pulse Current (8/20μs)	I _{pp}	100	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±30 ±30	KV
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM	--	--	2.5	V	Any I/O pin to ground
Breakdown Voltage	VBR	2.8	--	--	V	I _T = 1mA,Any I/O pin to ground
Reverse Leakage Current	IR	--	--	1	uA	VRWM=2.5V,Any I/O pin to ground
Clamping Voltage	VC	--	--	5	V	I _{pp} =1A(8x 20us pulse), Any I/O pin to ground
Clamping Voltage	VC	--	--	6	V	I _{pp} =10A(8x 20us pulse), Any I/O pin to ground
Clamping Voltage	VC	--	--	10	V	I _{pp} =100A(8x 20us pulse), Any I/O pin to ground
Forward Voltage	VF	--	--	1.2	V	I _F = 15 mA
Junction Capacitance	C _{vo-GND}	--	--	5	pF	VR=0V,f=1MHz, Any I/O to GND
	C _{I/O- I/O}	--	2	--	pF	VR=0V,f=1MHz, between I/O pins

Characteristic Curves

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve



Package Outline & Dimensions

SOP-8



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°