

注: 未经许可禁止传播、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N. NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2.withstanding voltage: AC1600V/1Min

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	15A	/

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Solder Pin: Brass (Sn Plated)

NOTES3:




1.Pitch: 7.62mm Poles: 02-24P

2.Operating temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$


3.RoHS Compliance

How to order

MX2EDGVC	-	7.62	-	XXP	-	XXXX	-	X	-	X	A-Z其他定制
产品型号		间距		极数		01:常规颜色 02-99: 定制颜色					
				颜色:		灰色:GY 橙色:OE 蓝色:BU 红色:RD 黑色:BK 透明色:TT 绿色:GN 黄色:YW 透明色:TT 白色:WE					
											Cu:铜 Fe:铁



PCB Layout



Pitch Range In mm			Nominal Dimension Range In mm							—	⌒	▤
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150			0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30			±2°		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	23.06.20	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE						
	CIXI MAIXU ELECTRONICS CO.,LTD.			NAME	MX2EDGVC-7.62-XXP			
	慈溪市迈旭电子有限公司			DWGNO.				