



NOTE:  
1.MATERIAL:  
a.HOUSING:ABS BLACK  
b.TERMINAL:BRASS  
c.PC PIN:STEEL  
(SURFACE PLATING: Ni-PLATING)  
SEE ORDERING INFORMATION  
2.ELECTRIC:  
a.CONTACT RESISTANCE: 100 MILLIOHMS MAX  
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN  
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE  
d.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION  
BC-12-A5BJ003

电池盒

BC-12系列

DIP 90° TYPE




PLATING:  
A-Au1U"  
J-Ni-PLATING  
K-Sn-PLATING

MATERIAL:  
1A-PP BLACK  
1B-PA66 BLACK  
2A-PPA BROWN  
2B-PPA BLACK  
3A-PPS BROWN  
3B-PPS BLACK  
4A-LCP WHITE  
4B-LCP BLACK  
5B-ABS BLACK

工程部

2024-03-12

H. WANG



|     |           |      |          |                 |
|-----|-----------|------|----------|-----------------|
| 3   | PC PIN    | 2    | STEEL    | Ni-Plating      |
| 2   | TERMINAL  | 2    | BRASS    | Ni-Plating      |
| 1   | HOUSING   | 1    | ABS      | BLACK           |
| NO. | PART NAME | Q'TY | MATERIAL | PLATING & COLOR |

|                                                                    |                                 |                                                                              |             |           |                                                                                             |            |                     |                                   |
|--------------------------------------------------------------------|---------------------------------|------------------------------------------------------------------------------|-------------|-----------|---------------------------------------------------------------------------------------------|------------|---------------------|-----------------------------------|
| UNLESS OTHERWISE<br>SPECIFIED TOLERANCES                           |                                 | <div>MYOUNG美阳</div> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a> |             |           |                                                                                             |            |                     |                                   |
| DECIMALS:<br>X :±0.30<br>X.X :±0.25<br>X.XX :±0.20<br>X.XXX :±0.10 | ANGLES:<br>X :±1°<br>X.X :±0.5° | DSND                                                                         | WangHeng    |           | DATE                                                                                        | 2024-03-12 |                     | TITLE:<br>9V电池盒BC-12-1J Ni DIP 插针 |
|                                                                    |                                 | CHKD                                                                         | ZhouRuicai  |           | DATE                                                                                        | 2024-03-12 |                     |                                   |
|                                                                    |                                 | APVD                                                                         | XueShunyong |           | DATE                                                                                        | 2024-03-12 |                     | PART NO.:                         |
| WEIGHT:                                                            |                                 | SCALE:                                                                       |             | SIZE: A4  | VIEW:  |            | BC-12-A5BJ003       |                                   |
| SHEET 1 OF 1                                                       |                                 | UNIT: mm                                                                     |             | REV.: A/1 | OBJECT: MY                                                                                  |            | DRAW NO.:WD-CP-0386 |                                   |