



REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:HIGH TEMP NYLON+30%GF
b.CONTACT:SUS304, T=0.35MM
(SURFACE PLATING: Au-PLATING)
SEE ORDERING INFORMATION
2.ELECTRIC:
a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10°C~ +80°C



ORDERING INFORMATION
BH-14250-B5BA003

电池盒
电池型号
SMT 180° TYPE

PLATING:
A-Au-PLATING
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK
5A-PA9T BLACK
5B-HIGH TEMP
NYLON+30%GF BLACK

工程部
2024-05-08
H. WANG



PCB Layout Diagram
Top View

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL+	1	SUS304, T=0.35MM	Au-Plating
2	TERMINAL-	1	SUS304, T=0.35MM	Au-Plating
1	HOUSING	1	HIGH TEMP NYLON+30%GF	BLACK

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2024-05-08
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-05-08
X.X :±0.25	X.X :±0.5°	APVD	XueShunYong	DATE	2024-05-08
X.XX :±0.20		SCALE:	SIZE: A4	VIEW:	⊙ ⊠
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: 电池盒BH-14250-1J Au SMT 双负极弹片	
				PART NO.: BH-14250-B5BA003	
				DRAW NO.:WD-CP-0395	