


printed on 15 Apr 2022 15:11 (China Standard Time) from TE370380

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11NOV2020	V.T	I.Y
	A1	ECN-22-138897	08FEB2022	V.T	Z.Z
	A2	ECN-22-149094	12APR2022	V.T	Z.Z



NOTES:

1.RECEPTACLE 2375556-X MATES WITH 2375555-X PLUG (X=1, 2, 3, 4 FOR RELEVANT CODE).
RECEPTACLE 2-2375556-X MATES WITH 2-2375555-X PLUG (X=1, 2, 3, 4 FOR RELEVANT CODE).

2.MATERIAL: HOUSING: PBT GF30, BLACK
TPA: PBT GF30, SEE TABLE FOR COLOR

3.DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(19=2019)
MONTH: THIRD DIGIT , EXCLUDING I , A=JAN, B=FEB, C=MARCH...(K=OCTOBER)
DAY: FOURTH AND FIFTH DIGITS(14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(11=11AM)


4.PULL TPA TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF TPA BEING HIT TO END-LOCK POSITION.

5.REFER TO DRAWING DT04-DOVETAIL FOR CLIP INTERFACE DIMENSIONS, RECOMMEND MOUNTING CLIP PN LIST:.
PLASTIC VERSION PN:2355806-1.

6.WIRE NO

7. APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE:

2141114-1	TIN	GENERAL	0.35	Ø1.10~Ø1.40	963142-2	963143-1
2141114-3	SILVER	HIGH VIBRATION				
2141116-1	TIN	GENERAL				
2141116-3	SILVER	HIGH VIBRATION	0.5~0.75	Ø1.40~Ø1.90	963142-1	963143-1
2177610-1	TIN	GENERAL				
2177610-3	SILVER	HIGH VIBRATION	1.0~1.5	Ø1.90~Ø2.40	963142-1	963143-1
TERMINAL PN	TERMINAL PLATING	APPLICATION				
			WIRE SIZE (MM2)	INSULATION WIRES(MM)	SWS P/N	BLIND PLUG P/N



CODING A PN:2375556-1 (V0) 2-2375556-1 (HB)				CODING B PN:2375556-2 (V0) 2-2375556-2 (HB)				CODING C PN:2375556-3 (V0) 2-2375556-3 (HB)				CODING D PN:2375556-4 (V0) 2-2375556-4 (HB)			
1				1								BLUE	PBT-GF30	TPA, CODE D	2
	1				1							NATURAL	PBT-GF30	TPA, CODE C	
		1				1						GREEN	PBT-GF30	TPA, CODE B	
			1				1					YELLOW	PBT-GF30	TPA, CODE A	1
1												GRAY	PBT-GF30	HOUSING, CODE D	
	1											GRAY	PBT-GF30	HOUSING, CODE C	
		1										GRAY	PBT-GF30	HOUSING, CODE B	
			1									GRAY	PBT-GF30	HOUSING, CODE A	
				1								BLACK	PBT-GF30	HOUSING, CODE D	
					1							BLACK	PBT-GF30	HOUSING, CODE C	
						1						BLACK	PBT-GF30	HOUSING, CODE B	
							1					BLACK	PBT-GF30	HOUSING, CODE A	
QTY. REQUEST PER ASSY												COLOR	MATERIAL	DESCRIPTION	ITEM NO
11.9	11.9	11.9	11.9	12.4	12.4	12.4	12.4	WEIGHT OF EACH ASSY NO. (g)							
A	A	A	A	A	A	A	A	REVISION OF EACH ASSY NO.							
2-2375556-4 (HB)	2-2375556-3 (HB)	2-2375556-2 (HB)	2-2375556-1 (HB)	2375556-4 (V0)	2375556-3 (V0)	2375556-2 (V0)	2375556-1 (V0)	TE ASSEMBLY PN							

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH	
MATERIAL		FINISH	
-		-	
-		-	




DWN	V.TANG	11NOV2020
CHK	C.WAN	12NOV2020
APVD	I.YIN	12NOV2020
PRODUCT SPEC		
108-32189		
APPLICATION SPEC		
-		
WEIGHT		
-		
CUSTOMER DRAWING		

				NAME	
				SUPERSEAL PRO 8POS.RECP. ASSEMBLY MCON1.2,CB TEMINAL	
SIZE		CAGE CODE		DRAWING NO	
A2		00779		C=2375556	
RESTRICTED TO		SCALE		SHEET	
		2:1		1 OF 2	
				REV	
				A2	

printed on 15 Apr 2022 15:11 (China Standard Time) from TE370380

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



NOTES:

1.RECEPTACLE 1-2375556-X MATES WITH 1-2375555-X PLUG (X=1, 2, 3, 4 FOR RELEVANT CODE).
RECEPTACLE 3-2375556-X MATES WITH 3-2375555-X PLUG (X=1, 2, 3, 4 FOR RELEVANT CODE).

2.MATERIAL: HOUSING: PBT GF30, BLACK
TPA: PBT GF30, SEE TABLE FOR COLOR

3.DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(19=2019)
MONTH: THIRD DIGIT , EXCLUDING 1 , A=JAN, B=FEB, C=MARCH...(K=OCTOBER)
DAY: FOURTH AND FIFTH DIGITS(14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(11=11AM)





4.PULL TPA TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF TPA BEING HIT TO END-LOCK POSITION.

5.REFER TO DRAWING DT04-DOVETAIL FOR CLIP INTERFACE DIMENSIONS, RECOMMEND MOUNTING CLIP PN LIST:.
PLASTIC VERSION PN:2355806-1.

6.WIRE NO

7. APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE:

2141114-1	TIN	GENERAL	0.35	Ø1.10-Ø1.40	963142-2	963143-1
2141114-3	SILVER	HIGH VIBRATION				
2141116-1	TIN	GENERAL	0.5~0.75	Ø1.40-Ø1.90	963142-1	963143-1
2141116-3	SILVER	HIGH VIBRATION				
2177610-1	TIN	GENERAL	1.0~1.5	Ø1.90-Ø2.40	963142-1	963143-1
2177610-3	SILVER	HIGH VIBRATION				
TERMINAL PN	TERMINAL PLATING	APPLICATION	WIRE SIZE (MM2)	INSULATION WIRES(MM)	SWS P/N	BLIND PLUG P/N

															
CODING A PN:1-2375556-1 (V0) 3-2375556-1 (HB)				CODING B PN:1-2375556-2 (V0) 3-2375556-2 (HB)				CODING C PN:1-2375556-3 (V0) 3-2375556-3 (HB)				CODING D PN:1-2375556-4 (V0) 3-2375556-4 (HB)			
1				1					BLUE	PBT-GF30	TPA, CODE D			2	
	1				1				NATURAL	PBT-GF30	TPA, CODE C				
		1				1			GREEN	PBT-GF30	TPA, CODE B				
			1				1		YELLOW	PBT-GF30	TPA, CODE A				
1									GRAY	PBT-GF30	HOUSING, CODE D			1	
	1								GRAY	PBT-GF30	HOUSING, CODE C				
		1							GRAY	PBT-GF30	HOUSING, CODE B				
			1						GRAY	PBT-GF30	HOUSING, CODE A				
				1					BLACK	PBT-GF30	HOUSING, CODE D				
					1				BLACK	PBT-GF30	HOUSING, CODE C				
						1			BLACK	PBT-GF30	HOUSING, CODE B				
							1		BLACK	PBT-GF30	HOUSING, CODE A				
				QTY. REQUEST PER ASSY					COLOR	MATERIAL	DESCRIPTION			ITEM NO	
12.1	12.1	12.1	12.1	12.7	12.7	12.7	12.7	WEIGHT OF EACH ASSY NO. (g)							
A	A	A	A	A	A	A	A	REVISION OF EACH ASSY NO.							
3-2375556-4 (HB)	3-2375556-3 (HB)	3-2375556-2 (HB)	3-2375556-1 (HB)	1-2375556-4 (V0)	1-2375556-3 (V0)	1-2375556-2 (V0)	1-2375556-1 (V0)	TE ASSEMBLY PN							

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH	
MATERIAL -		FINISH -	

DWN V.TANG 11NOV2020	CHK C.WAN 12NOV2020	APVD J.YIN 12NOV2020
PRODUCT SPEC 108-32189		
APPLICATION SPEC -		
WEIGHT -		
CUSTOMER DRAWING		

				NAME SUPERSEAL PRO 6POS.RECP. ASSEMBLY MCON1.2,CB TEMINAL			
SIZE A2	CAGE CODE 00779	DRAWING NO C=2375556	RESTRICTED TO				
SCALE 2:1				SHEET 2	OF 2	REV A2	