

**Harvatek 3.0mm Round LED LAMP****HV-GY22009M-R2-L50**

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 1/14

## **DISCLAIMER**

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

## **LIFE SUPPORT POLICY**

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 2/14

## Compliance and Certification

ISO9002, QS9000 and ISO14001 Certified

RoHS Compliant



## Orderable Information


**H V - GY 22009 M - R2 - L50**

Series Name	Color Code	Remark
HV : HARVATEK	GY22009: 3.0mm Round LED LAMP, 5.2mm Lens. InGaN 525nm Green chip AlGaInP 590nm Yellow chip M : White Diffused R2-L50: HARVATEK Part No.	

## Features:

- Stable Color
- Popular 3.0mm through hole package, 5.2mm lens height.
- White Diffused lens.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 3/14

**Package Dimensions:****Notes:**

1. All dimensions are millimeters.
2. Tolerance is +/-0.25mm unless otherwise noted.
3. Specifications are subject to change without notice.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 4/14

**Absolute Maximum Ratings at Ta=25°C**

Parameter	Symbol		Rating	Unit
Forward Current	I <sub>F</sub>		30	mA
Operating Temperature	T <sub>opr</sub>		-40to+85	°C
Storage Temperature	T <sub>stg</sub>		-40to+85	°C
Soldering Temperature*1	T <sub>sol</sub>		260±5	°C
Reverse Voltage	V <sub>R</sub>		5	V
Power Dissipation	P <sub>d</sub>	G	100	mW
		Y	75	
Peak Forward Current*2	I <sub>FP</sub>	G	100	mA
		Y	75	

\*1:Soldering time  $\leq$  5 seconds. \*2:Pulse Width  $\leq$  100  $\mu$  s and Duty  $\leq$  1%.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 5/14

**Electrical and Optical Characteristic**

Parameter	Symbol		Condition	Min.	Typ.	Max.	Unit
Luminous Intensity	I <sub>V</sub>	G	I <sub>F</sub> =20mA	1800	/	2800	mcd
		Y		850	/	1300	
Viewing Angle	20 ½	G/Y	I <sub>F</sub> =20mA	/	70	/	Deg
Forward Voltage	V <sub>F</sub>	G	I <sub>F</sub> =20mA	/	3.0	3.6	V
		Y			2.0	2.4	
Peak Emission Wavelength	λ <sub>P</sub>	G	I <sub>F</sub> =20mA	/	520	/	nm
		Y		/	595	/	
Dominant Wavelength	λ <sub>d</sub>	G	I <sub>F</sub> =20mA	/	525	/	nm
		Y		/	590	/	
Spectral Line Half-Width	Δλ	G	I <sub>F</sub> =20mA	/	25	/	nm
		Y		/	20	/	
Reverse Current	I <sub>R</sub>	G/Y	V <sub>R</sub> = 5 V	/	/	10	μA

## Notes:

θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 6/14

**Specifications for Bin Grading:(G)**

I <sub>v</sub> (mcd)		
Grade	Min.	Max.
X	1800	2800

λ d (nm)		
Grade	Min.	Max.
2	518.5	521.5
3	520.5	523.5
4	522.5	525.5
5	524.5	527.5
6	526.5	529.5

## Notes:

1. Luminous intensity: +/-15%.
2. Wavelength: +/-1nm.

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 7/14

**Specifications for Bin Grading:(Y)**

I <sub>v</sub> (mcd)		
Grade	Min.	Max.
V	850	1300


λ d (nm)		
Grade	Min.	Max.
3	585	588
4	587	590
5	589	592
6	591	594
7	593	595
8	594	597

## Notes:

- 1.Luminous intensity:+/-15%.
- 2.Wavelength: +/-1nm.


Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 8/14

## Typical Electro-Optical Characteristics Curves(G)



Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 9/14

## Typical Electro-Optical Characteristics Curves(Y)




Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 10/14

## Soldering condition

1. Careful attention should be paid during soldering. When soldering, leave more than 2mm from solder joint to Led, and soldering beyond the base of the tie bar is recommended.
2. Avoiding applying any stress to the lead frame while the LED are at high temperature particularly when soldering.
3. Dip and hand soldering should not be done more than one time.
4. After soldering the LED, the epoxy bulb should be protected from mechanical shock or vibration until the LED return to room temperature.
5. A rapid-rate process is not recommended for cooling the LED down from the peak temperature.
6. Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LED.
7. Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

### • Recommended soldering conditions

Hand Soldering		Wave Soldering	
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	160°C Max. (120 sec Max.)
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max
Distance	2mm Min.(From solder joint to Led)	Distance	2mm Min. (From solder joint to Led)



Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 11/14

**Reliability test items and conditions:**

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD:3%

No	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Er
1	Solder Heat	TEMP:260°C±5 °C	10 SEC	76 PCS	Iv $\leq$ Ivt*0.5 or Vf $\leq$ U or Vf $\leq$ L	0/1
2	Temperature Cycle	H:+100°C 15min ↓ 5min L:-40°C 15min	300 CYCLES	76 PCS		0/1
3	Thermal Shock	H:+100°C 5min ↓ 10sec L:-10°C 5min	300 CYCLES	76 PCS		0/1
4	High Temperature Storage	TEMP:100°C	1000 HRS	76 PCS		0/1
5	Low Temperature Storage	TEMP:-40°C	1000 HRS	76 PCS		0/1
6	DC Operating Life	TEMP:25°C IF=20mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85%RH	1000 HRS	76 PCS		0/1



Note: Ivt: To test Iv value of the chip before the reliability test.

Iv: The test value of the chip that has completed the reliability test

U: Upper Specification Limit

L: Lower Specification Limit

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 12/14

**Packing Specification:**

Official Product	HV-GY22009M-R2-L50	Customer Part No.	Data Sheet No.
	*****	*****	HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Aug.24. 2021	Version of 1.0	Page 13/14

## Revision History

Official Product	HV-GY22009M-R2-L50 *****	Customer Part No. *****	Data Sheet No. HV-GY22009M-R2-L50
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.24. 2021	Version of 1.0