



1. Configuration & Dimensions: (Unit:mm)



SYMBOL	A	B	C	D	Q'Ty/Disc
ADT18W60	22.0Max	10.0Max	9.0±1.0	1.0±0.1	500

2. Electrical Schematics :



3. Part Number Code

ADT 18 W 60 X 451
 A B C D E F

A: Series Name Power Chokes
 B: Dimensions(mm) 18: 22.0 Max
 C: Materials W= Winding
 D: Thickness(mm) 60: 10.0Max
 E: Tolerance X: Min
 F: Inductance 451=450uH

4. Electrical Apecification & Test Instrumenis :

Part Number	Inductance (uH)	Tolerance	Test Frequency (KHz)	DC Resistance (mΩ)Max	Rated DC Current (A)Max
ADT18W60X451	450	Min	1KHz/1.0V	25	---