





RoHS
Compliant



ZONE	EC N.O.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18

Notes:

- 1.Current Rating: 12V&1A max.
- 2.Contact Resistance: 30mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature:-25°C to+85°C



Circuit Diagram



12	Separator	Thermoplastics	White or Black
11	Cover2		
10	Cover1		
9	Housing		
8	Sleeve	Copper Alloy	Ni 40u"Min. Plated Overall.
7	Spring Contact		Sn 60u"Min. On Solder& ContactArea; Ni 40u"Min. Plated Overall.
6	Switch B Contact		
5	Switch A Contact		Au1~3u" On Contact Area Sn 60u"Min. On Solder Tails Ni 40u"Min. Plated Overall.
4	Left Contact		
3	Right Contact		
2	Ground Contact		
1	Mic Contact		
Item	Name	Material	Description

LZG®

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE:	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL:	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.:	
DRAWING NO.:	ZB23035-06DBAP-A			SHEET	1/1

PART NAME	Audio 6Pin W/Switch(2Row Solder 4+2)
PART NO.	ZB23035-06DBAP-A

TOLERANCE UNLESS	0.0±0.3
OTHERWISE SPECIFIED:	0.00±0.2
	0.000±0.1

0.°±2°
0.0°±1°
0.00°±0.5°

UNIT: mm

