








RoHS
Compliant




ZONE	E C N . N O	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18

SPECIFICATIONS:



- 1.RATING: 12V, 1A .
- 2.CONTACT RESISTANCE:30mΩ OR LESSFOR INITIAL
- 3.VOLTAGE PROOF:500V AC FOR ONE MINUTE
- 4.DURABILITY:5,000 INSERTION/EXTRACTION CYCLES
- 5.INSETION FORCE:3.0KG MAX
- 6.WITHDRAWAL FORCE:0.3KG MIN
- 7.WATER PROOFNESS: THIS PRODUCT IS BASED ON IPX7(1m,30min)
- 8.USING PLUG: Ø3.5MM、3-POLE STEREO
9. OVAL RING
- 9-1. Hardness of silicone rubber: 70°
- 9-2. Horizontal flash 0.10mm max;Longitudinal flash 0.10mm max
- 10.HOUSING WITH O-RING'S SEAL AREA BURRS IS 0.05mm MAX.
- 11.FOR REFLOW SOLDERING LEAD-FREE PROCESS.
- 12.PACKAGING: TAPE & REEL.



Recommended PCB Layout(T=1.2)
Tolerance: ±0.05(TOP view)



□ : TERMINAL NO.



9	OVAL RING	SILICONE	COLOR GREEN	1
8	BOND	EPOXY	----	1
7	TERMINAL	C2680R-H T=0.2	Matte Sn 80u" Min; Ni 40u" Min underplate	2
6	TIP SPRING-2 [4]	C5210R-EH T=0.2	Matte Sn 80u" Min; Ni 40u" Min underplate	1
5	RING SPRING [3]	C5210R-EH T=0.2	Matte Sn 80u" Min; Ni 40u" Min underplate	1
4	TIP SPRING-1 [2]	C5210R-EH T=0.2	Matte Sn 80u" Min; Ni 40u" Min underplate	1
3	EARTH SPRING [1]	C5210R-EH T=0.2	Matte Sn 80u" Min; Ni 40u" Min underplate	1
2	COVER	PA9T 94V-0	COLOR BLACK	1
1	HOUSING	PA9T 94V-0	COLOR BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

LZG®

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB23008-06SBAP-A			SHEET	1/1

PART NAME	WATERPROOF Ø3.5 PHONE JACK
PART NO.	ZB23008-06SBAP-A

TOLERANCE UNLESS OTHERWISE SPECIFIED:	0.0±0.30 0.00±0.20 0.000±0.10	0.°±2° 0.0°±1° 0.00°±0.5°	UNIT: mm
---------------------------------------	-------------------------------------	---------------------------------	----------