




Features

- ✧ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ✧ For surface mounted applications
- ✧ Low profile package
- ✧ Built-in strain relief
- ✧ Metal silicon junction, majority carrier conduction
- ✧ High surge capability
- ✧ High current capability, low forward voltage drop
- ✧ Low power loss, high efficiency
- ✧ For use in low voltage high frequency inverters, free wheeling and polarity protection applications
- ✧ Guardring for overvoltage protection
- ✧ High temperature soldering guaranteed: 250°C/10 seconds at terminals

SMB/DO-214AA



Dimensions in inches and (millimeters)

Mechanical Data

- ✧ Case: JEDEC SMC, molded plastic over passivated chip
- ✧ Polarity: Color band denotes cathode end
- ✧ Weight: 0.007 ounces, 0.21 gram

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS




Ratings at 25°C ambient temperature unless otherwise specified

		SS52	SS53	SS54	SS55	SS56	SS58	SS10	SS510	SS515	UNITS
Maximum recurrent peak reverse voltage	V _{RRM}	20	30	40	50	60	80	90	100	150	V
Maximum RMS voltage	V _{RWS}	14	21	28	35	42	56	63	70	105	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	80	90	100	150	V
Maximum average forw ord rectified current at T _L (SEE FIG.1) (NOTE 2)	I _(AV)	5.0									A
Peak forw ard surge current 8.3ms single half-sine-w ave superimposed on rated load(JEDEC Method)	I _{FSM}	175									A
Maximum instantaneous forw ard voltage at 5.0A(NOTE 1)	V _F	0.55			0.70		0.85			V	
Maximum DC reverse current @T _A =25°C at rated DC blockjing voltage(NOTE1) @T _A =100°C	I _R	0.5									mA
		20					10				
Typical thermal resitance (NOTE2)	R _{θ JA}	55									°C/W
	R _{θ JL}	17									
Operating junction temperature range	T _J	-55--- +150									°C
Storage temperature range	T _{STG}	-55--- +150									°C

NOTE: 1. Pulse test: 300 μs pulse width, 1% duty cycle

2. P.C.B. mounted with 0.55"X0.55" (14.0X14.0mm²) copper pad areas

Ratings AND Characteristic Curves

FIG.1 – FORWARD DERATING CURVE

FIG.2– PEAK FORWARD SURGE CURRENT

FIG.3 – TYPICAL FORWARD CHARACTERISTICS

FIG.4 – TYPICAL REVERSE CHARACTERISTICS
