


VOLTAGE RANGE: 50 --- 1000 V

CURRENT: 6.0 A

DO-27

Features

- ◇ Low cost
- ◇ Low leakage
- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ Easily cleaned with alcohol, Isopropanol and similar solvents
- ◇ The plastic material carries U/L recognition 94V-0



Dimensions in millimeters

Mechanical Data

- ◇ Case: JEDEC DO-27, molded plastic
- ◇ Polarity: Color band denotes cathode
- ◇ Weight: 0.041 ounces, 1.15 grams
- ◇ Mounting position: Any

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.

		HER 601	HER 602	HER 603	HER 604	HER 605	HER 606	HER 607	HER 608	UNITS
Maximum recurrent peak reverse voltage	V _{RRM}	50	100	200	300	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	210	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	300	400	600	800	1000	V
Maximum average forward rectified current 9.5mm lead length, @T _A =75°C	I _{F(AV)}	6.0								A
Peak forward surge current 8.3ms single half-sine-wave superimposed on rated load @T _J =125°C	I _{FSM}	200.0								A
Maximum instantaneous forward voltage @ 6.0A	V _F	1.0			1.3		1.7			V
Maximum reverse current @T _A =25°C at rated DC blocking voltage @T _A =100°C	I _R	10.0 200.0								μ A
Maximum reverse recovery time (Note1)	t _{rr}	60					75			ns
Typical junction capacitance (Note2)	C _J	100					65			pF
Typical thermal resistance (Note3)	R _{θJA}	12								°C/W
Operating junction temperature range	T _J	- 55 ---- + 150								°C
Storage temperature range	T _{STG}	- 55 ---- + 150								°C



NOTE: 1. Measured with $I_F=0.5A$, $I_R=1A$, $t_{rr}=0.25A$.

2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

3. Thermal resistance junction to ambient.

Ratings AND Characteristic Curves

FIG.1 -- TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



NOTES: 1. RISE TIME = 7ns MAX. INPUT IMPEDANCE = $1M\Omega$, 22pF.
2. RISE TIME = 10ns MAX. SOURCE IMPEDANCE = 50Ω .

SET TIME BASE FOR 10/20 ns/cm

FIG.2 -- TYPICAL FORWARD CHARACTERISTIC




FIG.3 -- FORWARD DERATING CURVE




FIG.4 -- TYPICAL JUNCTION CAPACITANCE




FIG.5 -- PEAK FORWARD SURGE CURRENT

