
**Version history**

Current version	Date	Author	Change description

Metallized polypropylene film interference suppression capacitor **(Class X1, 440Vac/480Vac)**

■ Outline Drawing



■ Features

- Metallized polypropylene structure
- Compact size
- Withstanding overvoltage stressing
- Excellent active and passive flame resistant abilities
- Used in across-the-line, interference suppression circuit.

■ Safety Approvals

• 	CQC	IEC 60384-14:2013, X1, 440Vac/480Vac, 0.0010μF ~ 10.0μF, 40/110/56/B Certificate No.: CQC06001016942
• 	ENEC-VDE	EN 60384-14:2013+A1:2016, X1, 440Vac/480Vac, 0.0010μF ~ 10.0μF, 40/110/56/B Certificate No.: 40021925
• 	UL/CUL	UL60384-14:2014, CSA E60384-14:09, X1, 440Vac/480Vac, 0.0010μF~10.0μF, 40/110/56/B File No.: E186600, CCN: FOWX2/8

■ Specifications

Class	Class X1		
Climatic Category / Passive Flammability Category	40/110/56/B		
Operating Temperature Range	-40°C ~ +110°C		
Rated Voltage (U _R)	440Vac/480Vac, 50/60Hz		
Maximum continuous DC voltage	1 000Vdc		
Capacitance Range	0.0010μF~10.0μF		
Capacitance Tolerance	±10%(K), ±20%(M)		
Voltage Proof	Between Terminals:	4.3U _R (dc), 2s	
	Between Terminals To Case:	2560 (Vac), 1min	
Insulation Resistance	R≥ 15 000MΩ , C _N ≤ 0.33μF RC _N ≥ 5 000s, C _N > 0.33μF (20°C, 100V ,1min)		
Dissipation Factor(tanδ)	0.0010μF<C _N ≤ 0.010μF	≤ 25×10 ⁻⁴ (1kHz,20°C)	≤ 25×10 ⁻⁴ (10kHz,20°C)
	0.010μF<C _N ≤ 0.47μF	≤ 15×10 ⁻⁴ (1kHz,20°C)	≤ 20×10 ⁻⁴ (10kHz,20°C)
	0.47μF<C _N ≤ 1.0μF	≤ 20×10 ⁻⁴ (1kHz,20°C)	≤ 40×10 ⁻⁴ (10kHz,20°C)
	1.0μF<C _N	≤ 30×10 ⁻⁴ (1kHz,20°C)	-----
Note: 1. If used in application which has ripple current applied, recommend to use AC filter series: C6A etc. If have any questions please contact our technical engineer for more detail; 2. For outdoor or severe humidity condition application, recommend to use THB series.			

■ Part number system

The 15 digits part number is formed as follow:

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
C	4	5												

Digit 1 to 3 Series code

C45=MKP65

Digit 4 to 5 A.C. rated voltage

S1=440V S3=480V

Digit 6 to 8 Rated capacitance value

For example : 103=10×10³ pF= 0.01μ F

Digit 9 Capacitance tolerance

K=±10%, M=±20%

Digit 10 Pitch

3=7.5 mm 4=10.0mm 6=15.0mm 9=22.5mm

B=27.5mm F=37.5mm M=52.5mm


Digit 11 Internal use

Digit 12 to 15 Lead form and packaging code

Table1 Lead form and packaging code

Digit 12		Digit 13		Digit 14		Digit 15	
code	explanation	code	explanation	code	explanation	code	explanation
A	ammo-pack	4 6	F=10.0mm F=15.0mm	0	straight	5	P3=25.4mm;H=18.5mm pitch=10/15mm) (For
C	straight lead "C" in the figure above	code	explanation	0 2		0 2	Length tolerance ±0.5mm Or standard length Length tolerance ±0.3mm
		00	standard lead length (18mm~26mm)				
		45	lead length 4.5mm				
		40	lead length 4.0mm				
		38	lead length 3.8mm				
		35	lead length 3.5mm				
		32	lead length 3.2mm				
T 3	P1=20.3mm ± 0.5mm P1=20mm±0.5mm	38 45	lead length 3.8mm lead length 4.5mm	0		0	Length tolerance ± 0.5mm or standard length

Note: Recommend short lead due to long lead could deform easily.



■ Dimensions(mm)

440Vac/480Vac#							440Vac/480Vac#							440Vac/480Vac#						
C _N (μ F)	W	H	T	P	d	Part number	C _N (μ F)	W	H	T	P	d	Part number	C _N (μ F)	W	H	T	P	d	Part number
0.0010	10.5	9.0	4.0	7.5	0.6	C45S1102-30****	0.056M	17.5	12.0	6.0	15.0	0.6	C45S1563M6S***	★ 1.0M	32.0	16.0	27.5	27.5	0.8	C45S1105MBC***
0.0012	10.5	9.0	4.0	7.5	0.6	C45S1122-30****	0.056K	17.5	12.0	7.0	15.0	0.6	C45S1563K6S****	★ 1.0K	32.0	18.5	31.0	27.5	0.8	C45S1105KBC****
0.0015	10.5	9.0	4.0	7.5	0.6	C45S1152-30****	0.068	17.5	13.5	7.5	15.0	0.6	C45S1683-6S****	1.0	32.0	28.0	17.0	27.5	0.8	C45S1105-BA****
0.0018	10.5	9.0	4.0	7.5	0.6	C45S1182-30****	0.068	17.5	12.0	13.0	15.0	0.8	C45S1683-6C****	1.0	32.0	30.0	16.0	27.5	0.8	C45S1105-BS****
0.0022	10.5	9.0	4.0	7.5	0.6	C45S1222-30****	0.082	17.5	14.0	8.0	15.0	0.6	C45S1823-6S****	1.2M	32.0	30.0	16.0	27.5	0.8	C45S1125MBS***
0.0027	10.5	9.0	4.0	7.5	0.6	C45S1272-30****	0.10M	17.5	14.0	8.0	15.0	0.6	C45S1104M6S***	1.2M	32.0	28.0	17.0	27.5	0.8	C45S1125MBA***
0.0033	10.5	9.0	4.0	7.5	0.6	C45S1332-30****	0.10K	17.5	14.5	8.5	15.0	0.6	C45S1104K6S****	1.2K	32.0	29.0	19.0	27.5	0.8	C45S1125KBA****
0.0039	10.5	9.0	4.0	7.5	0.6	C45S1392-30****	0.12	17.5	16.0	10.0	15.0	0.8	C45S1124-6S****	1.2K	32.0	33.0	18.0	27.5	0.8	C45S1125KBS****
0.0047	10.5	9.0	4.0	7.5	0.6	C45S1472-30****	0.15M	17.5	16.0	10.0	15.0	0.8	C45S1154M6S***	★ 1.5M	32.0	18.5	31.0	27.5	0.8	C45S1155MBC***
0.0056	10.5	9.0	4.0	7.5	0.6	C45S1562-30****	0.15K	17.5	19.0	11.0	15.0	0.8	C45S1154K6S****	1.5	32.0	33.0	18.0	27.5	0.8	C45S1155-BS****
0.0068	10.5	11.0	5.0	7.5	0.6	C45S1682-30****	0.18	17.5	19.0	11.0	15.0	0.8	C45S1184-6S****	1.8	32.0	37.0	22.0	27.5	0.8	C45S1185-BS****
0.0082	10.5	11.0	5.0	7.5	0.6	C45S1822-30****	0.039	26.5	15.0	6.0	22.5	0.8	C45S1393-90****	2.2M	32.0	37.0	22.0	27.5	0.8	C45S1225MBS***
0.010	10.5	11.0	5.0	7.5	0.6	C45S1103-30****	0.047	26.5	15.0	6.0	22.5	0.8	C45S1473-90****	0.33	41.0	22.0	11.0	37.5	1.0	C45S1334-F0****
0.012	10.5	12.0	6.0	7.5	0.6	C45S1123-30****	0.056	26.5	15.0	6.0	22.5	0.8	C45S1563-90****	0.39	41.0	22.0	11.0	37.5	1.0	C45S1394-F0****
0.015	10.5	12.0	6.0	7.5	0.6	C45S1153M30***	0.068	26.5	15.0	6.0	22.5	0.8	C45S1683-90****	0.47	41.0	22.0	11.0	37.5	1.0	C45S1474-FS****
0.0010	13.0	9.0	4.0	10.0	0.6	C45S1102-40****	0.082	26.5	15.0	6.0	22.5	0.8	C45S1823-9S****	0.56	41.0	22.0	11.0	37.5	1.0	C45S1564-FS****
0.0012	13.0	9.0	4.0	10.0	0.6	C45S1122-40****	0.10	26.5	15.0	6.0	22.5	0.8	C45S1104-9S****	0.68	41.0	22.0	11.0	37.5	1.0	C45S1684-FS****
0.0015	13.0	9.0	4.0	10.0	0.6	C45S1152-40****	0.12	26.5	15.0	6.0	22.5	0.8	C45S1124-9S****	0.82M	41.0	22.0	11.0	37.5	1.0	C45S1824MFS****
0.0018	13.0	9.0	4.0	10.0	0.6	C45S1182-40****	0.15	26.5	16.0	7.0	22.5	0.8	C45S1154-9S****	0.82K	41.0	24.0	13.0	37.5	1.0	C45S1824KFS****
0.0022	13.0	9.0	4.0	10.0	0.6	C45S1222-40****	0.18	26.5	17.0	8.5	22.5	0.8	C45S1184-9S****	1.0	41.0	24.0	13.0	37.5	1.0	C45S1105-FS****
0.0027	13.0	9.0	4.0	10.0	0.6	C45S1272-40****	0.22	26.5	17.0	8.5	22.5	0.8	C45S1224-9S****	1.0	42.0	15.0	24.0	37.5	1.0	C45S1105-FC****
0.0033	13.0	9.0	4.0	10.0	0.6	C45S1332-40****	0.27	26.5	18.5	10.0	22.5	0.8	C45S1274-9S****	1.2	41.0	26.0	15.0	37.5	1.0	C45S1125-FA****
0.0039	13.0	9.0	4.0	10.0	0.6	C45S1392-40****	0.33	26.5	20.0	11.0	22.5	0.8	C45S1334-9S****	1.2	42.0	28.0	14.0	37.5	1.0	C45S1125-FS****
0.0047	13.0	9.0	4.0	10.0	0.6	C45S1472-4S****	0.39	26.5	20.0	11.0	22.5	0.8	C45S1394-9S****	1.5M	41.0	26.0	15.0	37.5	1.0	C45S1155MFA****
0.0056	13.0	9.0	4.0	10.0	0.6	C45S1562-4S****	0.47M	26.5	22.0	12.0	22.5	0.8	C45S1474M9S***	1.5M	42.0	28.0	14.0	37.5	1.0	C45S1155MFS****
0.0068	13.0	9.0	4.0	10.0	0.6	C45S1682-4S****	0.47K	26.5	23.0	13.5	22.5	0.8	C45S1474K9S****	1.5K	41.0	30.0	16.0	37.5	1.0	C45S1155KFS****
0.0082	13.0	9.0	4.0	10.0	0.6	C45S1822-4S****	0.56M	26.5	23.0	13.5	22.5	0.8	C45S1564M9S***	1.5	42.0	19.0	24.0	37.5	1.0	C45S1155-FC****
0.010	13.0	9.0	4.0	10.0	0.6	C45S1103-4S****	0.56K	26.5	24.5	15.5	22.5	0.8	C45S1564K9S****	1.8M	41.0	30.0	16.0	37.5	1.0	C45S1185MFS****
0.012	13.0	11.0	5.0	10.0	0.6	C45S1123-4S****	0.68M	26.5	24.5	15.5	22.5	0.8	C45S1684M9S***	1.8K	41.0	32.0	17.0	37.5	1.0	C45S1185KFS****
0.015	13.0	11.0	5.0	10.0	0.6	C45S1153-4S****	0.15	32.0	18.0	9.0	27.5	0.8	C45S1154-B0****	2.2M	41.0	32.0	17.0	37.5	1.0	C45S1225MFA****
0.018	13.0	11.0	5.0	10.0	0.6	C45S1183-4S****	0.18	32.0	18.0	9.0	27.5	0.8	C45S1184-B0****	2.2	41.0	33.5	18.5	37.5	1.0	C45S1225-FS****
0.022	13.0	11.0	5.0	10.0	0.6	C45S1223-4S****	0.22	32.0	18.0	9.0	27.5	0.8	C45S1224-B0****	2.7	41.0	37.0	22.0	37.5	1.0	C45S1275-FS****
0.027	13.0	12.0	6.0	10.0	0.6	C45S1273-4S****	0.27	32.0	18.0	9.0	27.5	0.8	C45S1274-BS****	3.3M	41.0	37.0	22.0	37.5	1.0	C45S1335MFS****
0.033	13.0	12.0	6.0	10.0	0.6	C45S1333-4S****	0.33	32.0	18.0	9.0	27.5	0.8	C45S1334-BS****	3.3K	41.0	41.0	26.0	37.5	1.0	C45S1335KFS****
0.039	13.0	13.0	7.0	10.0	0.6	C45S1393-4S****	0.33	32.0	12.0	18.0	27.5	0.8	C45S1334-BC****	3.3K	41.5	37.5	27.5	37.5	1.0	C45S1335KFA****
0.047	13.0	13.0	7.0	10.0	0.6	C45S1473M4S***	0.39	32.0	20.0	11.0	27.5	0.8	C45S1394-BS****	3.9	41.0	41.0	26.0	37.5	1.0	C45S1395-FS****
0.047K	13.0	14.0	8.0	10.0	0.6	C45S1473K4S****	0.47	32.0	20.0	11.0	27.5	0.8	C45S1474-BS****	3.9	41.5	37.5	27.5	37.5	1.0	C45S1395-FA****
0.056	13.0	14.0	8.0	10.0	0.6	C45S1563-4S****	★ 0.47	32.0	12.0	22.0	27.5	0.8	C45S1474-BC****	4.7M	41.0	43.0	28.0	37.5	1.0	C45S1475MFS****
0.010	17.5	9.5	5.0	15.0	0.6	C45S1103-6S****	0.56	32.0	22.0	13.0	27.5	0.8	C45S1564-BS****	4.7K	42.0	45.0	30.0	37.5	1.0	C45S1475KFS****
0.012	17.5	9.5	5.0	15.0	0.6	C45S1123-6S****	0.68M	32.0	22.0	13.0	27.5	0.8	C45S1684MBS***	★ 4.7	57.0	38.0	24.0	52.5	1.2	C45S1475-MST***
0.015	17.5	9.5	5.0	15.0	0.6	C45S1153-6S****	0.68K	32.0	25.0	13.0	27.5	0.8	C45S1684KBA****	5.6	57.0	45.0	30.0	52.5	1.2	C45S1565-MST***
0.018	17.5	9.5	5.0	15.0	0.6	C45S1183-6S****	0.68K	32.0	24.5	15.0	27.5	0.8	C45S1684KBS****	6.8	57.0	45.0	30.0	52.5	1.2	C45S1685-MST***
0.022	17.5	9.5	5.0	15.0	0.6	C45S1223-6S****	★ 0.68	32.0	16.0	22.0	27.5	0.8	C45S1684-BC****	6.8	57.0	30.0	44.0	52.5	1.2	C45S1685-MCT**
0.027	17.5	11.0	5.0	15.0	0.6	C45S1273-6S****	0.82M	32.0	25.0	13.0	27.5	0.8	C45S1824MBS***	8.2	57.0	50.0	35.0	52.5	1.2	C45S1825-MST***
0.033	17.5	11.0	5.0	15.0	0.6	C45S1333-6S****	0.82K	32.0	24.5	15.0	27.5	0.8	C45S1824KBS****	10.0	57.0	50.0	35.0	52.5	1.2	C45S1106-MST***
0.039	17.5	12.0	6.0	15.0	0.6	C45S1393-6S****	0.82K	32.0	28.0	14.0	27.5	0.8	C45S1824KBA****							
0.047	17.5	12.0	6.0	15.0	0.6	C45S1473-6S****														

- Note: 1. "-" = capacitance tolerance code, M=±20%,K=±10%
2. "****" = lead form and packaging code (refer to table 1)
3. "#" when the rated voltage is 480Vac,the digit 4~5 is S3.
4. "★" = Arc bottom of the outer shell

■ Maximum permissible voltage change per unit of time

Rated Voltage (Vac)	dV/dt(V/us) at 680 Vdc				
	P=10mm	P=15mm	P=22.5mm	P=27.5mm	P=37.5mm
440	750	600	300	225	150

Note: 1. Rated voltage pulse slope $(dV/dt)_R$ at rated voltage.

2. If the working voltage(U) is lower than the rated voltage(U_R),the capacitor can be worked at a higher dV/dt. In this case, the maximum allowed dV/dt is obtain by multiplying the right value with U_R/U .

■ Test Method And Performance (IEC 60384-14)

Group	Item		Conditions of test	Performance requirements
A1	4.1 Visual examination		Dimensions: gauging by vernier caliper	No visible damage & legible marking
	4.1Dimensions(Gauging)			Fit detail specification
A2	4.2.2 Capacitance		Measuring frequency: Capacitance: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz Voltage proof between terminals: 4.3UR(d.c.), 1min IR. test voltage: 100Vd.c.	Within specified tolerance
	4.2.3 Tangent of loss angle			No permanent breakdown or flashover
	4.2.1 Voltage proof			I.R.:≥ the rated value
	4.2.5 Insulation Resistance			
B1	4.5 Solderability		Methods: Groove welding Ta, Method 1 Solder temperature: 245°C±5°C Immersion time: 2.0s±0.5s	Good quality of tinning
C1A	Initial measu remen t	4.1Visual examination	Dimensions: gauging by vernier caliper Measuring frequency: Capacitance: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz	No visible damage & legible marking
		4.1Dimensions(Gauging)		Fit detail specification
		4.2.2Capacita nce		Within specified tolerance
		4.2.3Tangent of loss angle		
	4.1.1 Creepage distances and Clearances		Gauging by vernier caliper	Creepage distances≥ 4.0mm Clearances≥ 3.0mm
	4.3 Robustness of Terminations (straight lead)		Tense: 0.50 < d≤ 0.80, 10N 0.80 < d≤ 1.25, 20N Ub bending test: Bend: 0.50 < d≤ 0.80, 5N 0.80 < d≤ 1.25, 10N The terminals shall be bent 2 times in each direction	No visible damage
	4.4 Resistance to Soldering heat		Capacitors are not pre-dried Groove Method Tb, Method 1A Solder temperature: 260°C±5°C Immersion time: 10s±1s	No visible damage & legible marking
	4.19 Component solvent resistance		Solvent: industrial isopropyl Solvent temperature:23°C±5°C Dipping time:5min±0.5min Method 2: (without Sassafras test) Recovery time: 48h	Comply with the specifications in the product size table
	Final measurement		Appearance inspection Cap. measuring frequency: 1kHz Tangent of loss angle: CN≤ 1μF: 10kHz; CN > 1μF: 1kHz	No visible damage Cap.: ΔC /C≤ 5% Tangent of loss angle: CN≤ 1μF: ≤ 0.008 (10kHz) CN > 1μF: ≤ 0.005 (1kHz)

Group	Item		Conditions of test	Performance requirements
C1B	Initial measurement	4.1 Visual examination	Dimensions: gauging by vernier caliper Measuring frequency: Capacitance: 1kHz Tangent of loss angle: $C_N \leq 1\mu F$: 10kHz; $C_N > 1\mu F$: 1kHz	No visible damage & legible marking
		4.1 Dimensions (Gauging)		Fit detail specification
		4.2.2 Capacitance		Within specified tolerance
		4.2.3 Tangent of loss angle		
	4.5 Solderability		Methods: Groove welding Ta, Method 1 Solder temperature: $245^{\circ}\text{C} \pm 5^{\circ}\text{C}$ Immersion time: $2.0\text{s} \pm 0.5\text{s}$	Good quality of tinning
	4.20 Solvent resistance of the marking		Solvent: Industrial isopropanol. Solvent temperature: $23^{\circ}\text{C} \pm 5^{\circ}\text{C}$ Dipping time: $5\text{min} \pm 0.5\text{min}$ Condition: scrub Scrub material: absorbent cotton Reverting time: No	The marking shall be legible
	4.6 Rapid change of temperature		$T_A = -40^{\circ}\text{C}$, $T_B = +110^{\circ}\text{C}$ 5 cycles, Duration: $t = 30\text{min}$	No visible damage
	4.7 Vibration (straight lead) (when capacitor weight > 3g, the capacitor body needs to be fixed)		Amplitude 0.75mm or acceleration 98m/s^2 (whichever is the smaller severity), f: 10Hz to 500Hz. Three directions, 2h for each direction, total 6h.	No visible damage
C1	4.11 Climatic sequence	4.8 Bump (straight lead) (when capacitor weight > 3g, the capacitor body needs to be fixed)	4 000 times, Acceleration: 400m/s^2 , Pulse duration, 6ms	No visible damage
		Final measurement	Appearance inspection Cap. measuring frequency: 1kHz	No visible damage Cap.: $ \Delta C /C \leq 5\%$
		Initial measurement	According to the conditions of Group C1A and C1B	According to the requirements of Group C1A and C1B
		Dry heat	$+110^{\circ}\text{C}$, 16h	No visible damage & legible marking
		Damp heat, Cyclic	Test Db, Severity: b, the first cycle Temperature: $+55^{\circ}\text{C}$, 24h each cycle, Method 2	
		Cold	-40°C , 2h	
		Damp heat, Cyclic	Test Db, Severity b, the other cycles Temperature: $+55^{\circ}\text{C}$, 24h each cycle, Method 2	Cap.: $ \Delta C /C \leq 5\%$ Increase of $\text{tg}\delta$: $C_N \leq 1\mu F$: ≤ 0.008 (10kHz) $C_N > 1\mu F$: ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: $\geq 50\%$ of the rated value
		Final measurement	Measuring frequency: Capacitance: 1kHz Tangent of loss angle: $C_N \leq 1\mu F$: 10kHz; $C_N > 1\mu F$: 1kHz Voltage proof between terminals: $4.3U_R(\text{d.c.}), 1\text{min}$ Voltage proof between terminal and housing: $2U_R + 1500\text{V}(\text{a.c.}), 1\text{min}$ Insulation resistance test voltage: 100Vd.c.	

Group	Item	Conditions of test	Performance requirements
C2	4.12 Damp heat, steady state	Temperature: 40°C ±2°C Humidity: 93±3%RH Duration: 56 days	No visible damage & legible marking Cap.: ΔC /C ≤ 5% Increase of tgδ: C _N ≤ 1μF: ≤ 0.008 (10kHz) C _N > 1μF: ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: ≥ 50% of the rated value
	Final measurement	Tangent of loss angle: C _N ≤ 1μF: 10kHz; C _N > 1μF: 1kHz Voltage proof between terminals: 4.3U _R (d.c.),1min Voltage proof between terminal and housing: 2U _R +1500V(a.c.),1min Insulation resistance test voltage: 100Vd.c.	
C3	Initial measurement	Measuring frequency capacitance: 1kHz Tangent of loss angle: C _N ≤ 1μF: 10kHz; C _N > 1μF: 1kHz Insulation resistance test voltage: 100Vd.c.	Within specified tolerance
	4.13 Impulse voltage	Each individual capacitor shall be subjected to 24 impulses of the same polarity, the time between impulses shall not be less than 10s, and the peak value of the voltage impulse: 4.0kV (suitable for C _N ≤ 1μF; When C _N > 1μF, the capacitor can endure pulse voltage value is 4.0/√C _N kV)	There are three or more waveforms which indicate that no self-heating breakdown have occurred when it is monitored by the monitor (when any three successive impulses are shown by the monitor to have a wave form indicating that no self-heating breakdown have taken place the impulses can be stopped)
	4.14 Endurance	Temperature : +110°C Duration : 1000h Voltage: at 1.25 U _R except that once every hour the voltage shall be increased to 1000Vrms for 0.1s; and each capacitor individually through a resistor of 47.0Ω ± 5 %.	No visible damage & legible marking Cap.: ΔC /C ≤ 10% Increase of tgδ: C _N ≤ 1μF: ≤ 0.008 (10kHz) C _N > 1μF: ≤ 0.005 (1kHz) No permanent breakdown or flashover I.R.: ≥ 50% of the rated value
	Final measurement	Tangent of loss angle: C _N ≤ 1μF: 10kHz; C _N > 1μF: 1kHz Voltage proof between terminals: 4.3U _R (d.c.),1min Voltage proof between terminal and housing: 2U _R +1500V(a.c.),1min	

Group	Item	Conditions of test	Performance requirements
C4	4.15 Charging and discharging	Times: 10 000 Duration of charging: 0.5s Duration of discharging: 0.5s Charging voltage: $\sqrt{2}U_R$ Vd.c. Charging resistance: $220/C_N(\Omega)$ or the current $\leq 1.0A$ (whichever is the minor) Discharging resistance: $R = \frac{\sqrt{2}U_R}{C_N \times \frac{dU}{dt}} (\Omega)$ C_N : Capacitance (μF) $dU/dt(V/us)$: $100V/\mu s$	Cap.: $ \Delta C /C \leq 10\%$ Increase of tg δ : $C_N \leq 1\mu F$: ≤ 0.008 (10kHz) $C_N > 1\mu F$: ≤ 0.005 (1kHz) I.R.: $\geq 50\%$ of the rated value
C6	4.17 Passive flammability	Needle flame test The category of flammability: B Expose time: 1 time Capacitor Volume Exposing time $250 < V(mm^3) \leq 500$ 20s $500 < V(mm^3) \leq 1750$ 30s $V(mm^3) > 1750$ 60s	The flaming time of each capacitor shall not go beyond 10s after it is taken apart from the flame. Drop of each capacitor caused by flame shall not fire the tissue below.
C7	4.18 Active flammability	The specimens shall be individually wrapped in at least 1, but not more than 2, complete layers of cheesecloth, the cheesecloth shall be untreated pure cotton cloth. Each sample shall be subjected to 20 discharged, the interval between successive discharges shall be 5s. $U_i = 4.0kV_0^{+7}\%$ U_R be applied and be maintained for 120_0^{+10} s after the last discharge.	The cheese cloth around the capacitor shall not burn with a flame.

■ Marking (For example)

 MKP65 440~ X1
 104K 40/110/56/B



$P \leq 27.5\text{mm}$

 MKP65 440~475M X1
 40/110/56/B L50005



$P > 27.5\text{mm}$

Marking Introduction:

Sign	explain	Sign	explain
	Brand	40/110/56/B	Climate category / Passive Flammability Class
MKP65	Type		CQC Approval
440~	Rated voltage		ENEC-VDE Approval
X1	Class		UL&CUL Approval
104K 475M	Rated capacitance and tolerance	L50005	Product traceability information

■ Taping specification for box-type capacitors

▲ Outline Drawing




Fig.1 P=5.0, 7.5mm




Fig.2 P=10.0, 15.0mm

▲ Taping Dimensions(mm)

Technology index title	Code	Dimensions				Tolerance
		P=5.0	P=7.5	P=10.0	P=15.0	
Taping type	—	Fig 1	Fig 1	Fig2	Fig 2	—
Part number Digit12-15	Ammo-pack	A201	A301	A405	A605	
Taping pitch	P ₃	12.7	12.7	25.4	25.4	±1.0
Feed hole pitch	P ₀	12.7	12.7	12.7	12.7	±0.3
Center of wire	P ₁	3.85	2.6	7.7	5.2	±0.7
Center of body	P ₂	6.35	6.35	12.7	12.7	±1.3
Pitch of taping wire	F ^{**}	5.0	7.5	10.0	15.0	+0.6 -0.1
Component alignment	△ S	0	0	0	0	±2.0
Height of component from tape center	H ^{***}	18.5	18.5	18.5	18.5	±0.5
Carrier tape width	W	18.0	18.0	18.0	18.0	+1.0 -0.5
Hold down tape width	W ₀	6min	10min	10min	10min	—
Hole position	W ₁	9.0	9.0	9.0	9.0	±0.5
Hold down tape sition	W ₂	3max	3max	3max	3max	—
Feed hole dia.	D ₀	4.0	4.0	4.0	4.0	±0.2
Tape thickness	t	0.7	0.7	0.7	0.7	±0.2

Note: * P₀=15mm is also available;

**F can be other lead spacing;


***H=16.5mm is available;

■ Soldering suggestions


- ▲ Manual soldering
Max. temperature: 350°C, time: 3s
- ▲ Wave soldering

There are many factors affecting the heating of film capacitor during the wave soldering process, such as: preheating temperature, preheating time, soldering temperature, soldering time, other heat sources influence and so on.

The typical soldering profile is as below:



▲ Because overheating could damage the capacitor, we recommend paying attention to the maximum capacitor temperature and heating time, use temperature sensor to detect the maximum capacitor body temperature.




Note: If re-working or dipping twice is necessary, it should be done after the capacitor returns to the normal temperature.


Temperature sensor position (Tcapacitor body)	The capacitor body surface of lead side, capacitor height position from PCB: h1=2 ~ 3mm		
Maximum capacitor body temperature Tp(°C)	OPP film P ≤ 15mm	OPP film P > 15mm	PET film
	115	120	125
Maximum capacitor lead wire temperature (°C)	265	265	265
Maximum capacitor body heating time tp=Tp-5°C	30s		

■ Packing box sizes(mm)(example)


1. Out packing box for bulk



2. Inner packing box for bulk



3. Box sizes for Ammo-pack



■ Storage conditions

▲ It must be noted that the solderability of the terminals may be deteriorated when stored in an atmosphere filled with moisture, dust, or a reactive oxidizing gas.(hydrogen chloride, hydrogen sulfide, sulfuric acid,etc.)

▲ It shouldn't be located in particularly high temperature and high humidity, it must submit to the following conditions(unchanging primal package):

Temperature: -40 °C to 35 °C

Humidity: Average per year ≤ 70%RH;

For 30 full days randomly distributed throughout the year ≤ 80%RH

Storage time for tinned lead wire: (from the date marked on the capacitor's body or the label glued to the package) :

Bulk(packed with plastic bag): ≤ 24 months ;

Taping and line up: ≤ 12 months