








RoHS
Compliant





Circuit Diagram



P/N	DIM.A	DESCRIPTION
ZB30018-03DBAP-A	板上 CH 3.20mm	防水 or 不防水
ZB30018-03DBAP-B	沉板 CH 2.20mm	防水 or 不防水
ZB30018-03DBAP-C	沉板 CH 1.40mm	防水 or 不防水

5525 Plug Drawing



- Notes:
- 1.Current Rating: 20V&10A Max.
 - 2.Contact Resistance: 50mOhms Max.(initial)
 - 3.Insulation Resistance: 100M Ohms Min./500V DC
 - 4.Dielectric Withstanding Voltage: 500V AC/1Minute
 - 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
 - 6.Durability: 5,000 Cycles
 - 7.Operating Temperature:-25°C to+85°C



7	BOND	EPOXY	Black
6	Cover	Hight.	Black;UL 94-V0
5	Housing	Thermoplastics	
4	Shell		
3	Switch(-)		
2	Spring(-)	Copper Alloy	Ni Plated OverAll
1	Center Pin(+)		
Item	Name	Material	Description

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2025.01.14	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.01.14	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.01.14	DWG. NO.	
DRAWING NO.	ZB30018-03DBAP-A	SHEET	1/1		

PART NAME	DC POWER JACK	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT:	
PART NO.	ZB30018-03DBAP-A	OTHERWISE SPECIFIED:	0.00±0.20 0.000±0.10	0.0°±1° 0.00°±0.5°	mm	