



1. Configuration & Dimensions : (Unit:mm)



SYMBOL	A	B	C	D	E	F	Q'Ty/Disc
ADTB17W70	22.0Max	12.0Max	4.0±1.0	1.0±0.1	1.0Max	6.5Ref	200

2. Electrical Schematics



Winding order	Origination	Parameter
N	S-F	2UEWΦ1.0mm*21.5TS

3. Part Number Code

ADTB 17 W 70 M 330 - B
 A B C D E F G

A: Series Name Power Chokes
 B: Dimensions(mm) 17: 22.0 Max
 C: Materials W= Horizontal
 D: Thickness(mm) 70: 12.0 Max
 E: Tolerance M: ±20%
 F: Inductance 330=33uH
 G: Internal controls

4. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Test Frequency (Hz)	DC Resistance (mΩ)Max.	Current (A)Max.
ADTB17W70M330-B	33.0	±20%	1KHz/0.25V	25.0	10.0

Notes:

- 1) All test data is referenced to 25°C ambient.
- 2) Operating temperature range -25°C to +105°C,(Including self - temperature rise).