

Harvatek 3.0mm Round LED LAMP with Holder**HV-32690/230/2SYGUYC**

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 1/14

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 2/14

Compliance and Certification

ISO9002, QS9000 and ISO14001 Certified

RoHS Compliant



Orderable Information

H V - 32690 / 230 / 2SYGUYC


Series Name	Color Code	Remark
HV : HARVATEK	32690:Array 2 Lamp 230: 3.0mm Round LED LAMP. 2SYGUY: AlGaInP 570nm Green Chip. AlGaInP 590nm Yellow Chip. C: Water Clear	

Features:

- Stable Color
- Popular 3.0mm through hole package.
- Water Clear Lens.

Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3
			Page 3/14

Package Dimensions:



Notes:

- 1.All dimensions are millimeters.
- 2.Tolerance is +/-0.25mm unless otherwise noted.
- 3.Specifications are subject to change without notice.

Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3
			Page 4/14

Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Rating	Unit
Forward Current	I_F	30	mA
Operating Temperature	T_{opr}	-40to+85	°C
Storage Temperature	T_{stg}	-40to+85	°C
Soldering Temperature*1	T_{sol}	260±5	°C
Power Dissipation	P_d	75	mW
Reverse Voltage	V_R	1.1	V
Peak Forward Current*2	I_{FP}	75	mA

*1:Soldering time \leq 5 seconds. *2:Pulse Width \leq 100 μ s and Duty \leq 1%

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 5/14

Electrical and Optical Characteristic

Parameter	Symbol	Condition		Min.	Typ.	Max.	Unit
Forward Voltage	V_F	$I_F=20\text{ mA}$		/	2.0	2.4	V
Reverse Current	I_R	$V_R=1.1\text{ V}$		/	/	10	μA
Luminous Intensity	I_V	$I_F=20\text{ mA}$	G	80	180	/	mcd
			Y	100	300	/	
Viewing Angle	$2\theta_{1/2}$	$I_F=20\text{ mA}$	G/Y	/	55	/	deg
Dominant Wavelength	λ_d	$I_F=20\text{ mA}$	G	/	570	/	nm
			Y	/	590	/	
Peak Wavelength	λ_p	$I_F=20\text{ mA}$	G	/	575	/	nm
			Y	/	595	/	
Spectrum Radiation Bandwidth	$\Delta\lambda$	$I_F=20\text{ mA}$	G	/	20	/	nm
			Y	/	18	/	

Notes:

$\theta_{1/2}$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 6/14

Specifications for Bin Grading:(G)

I _v (mcd)		
Grade	Min.	Max.
Q	80	125
R	100	200
S	160	320
T	250	500

λ d (nm)		
Grade	Min.	Max.
5	566	569
6	568	571
7	570	573
8	572	575
9	574	577

Notes:

- 1.Luminous intensity: +/-15%.
- 2.Wavelength: +/-1nm.

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 7/14

Specifications for Bin Grading:(Y)

I _v (mcd)		
Grade	Min.	Max.
R	100	200
S	160	320
T	250	500
U	400	800
V	630	1250


λ d (nm)		
Grade	Min.	Max.
3	585	588
4	587	590
5	589	592
6	591	594
7	593	595
8	594	597

Notes:

- 1.Luminous intensity: +/-15%.
- 2.Wavelength: +/-1nm.


Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 8/14

Typical Electro-Optical Characteristics Curve(G)



Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3
		Page 9/14	

Typical Electrical / Optical Characteristics Curves(Y)




Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3
			Page 10/14

Soldering condition

- Careful attention should be paid during soldering. When soldering, leave more than 2mm from solder joint to Led, and soldering beyond the base of the tie bar is recommended.
- Avoiding applying any stress to the lead frame while the LED are at high temperature particularly when soldering.
- Dip and hand soldering should not be done more than one time.
- After soldering the LED, the epoxy bulb should be protected from mechanical shock or vibration until the LED return to room temperature.
- A rapid-rate process is not recommended for cooling the LED down from the peak temperature.
- Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LED.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

• Recommended soldering conditions

Hand Soldering		Wave Soldering	
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	160°C Max. (120 sec Max.)
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max
Distance	2mm Min.(From solder joint to Led)	Distance	2mm Min. (From solder joint to Led)



Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3
		Page 11/14	

Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD:3%

No	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Er
1	Solder Heat	TEMP:260℃±5℃	10 SEC	76 PCS	$I_v \leq I_{vt} * 0.5$ or $V_f \geq U$ or $V_f \leq L$	0/1
2	Temperature Cycle	H:+100℃ 15min ∫ 5min L:-40℃ 15min	300 CYCLES	76 PCS		0/1
3	Thermal Shock	H:+100℃ 5min ∫ 10sec L:-10℃ 5min	300 CYCLES	76 PCS		0/1
4	High Temperature Storage	TEMP:100℃	1000 HRS	76 PCS		0/1
5	Low Temperature Storage	TEMP:-40℃	1000 HRS	76 PCS		0/1
6	DC Operating Life	TEMP:25℃ IF=20mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85℃/85%RH	1000 HRS	76 PCS		0/1


Note: I_{vt} : To test I_v value of the chip before the reliability test.






I_v : The test value of the chip that has completed the reliability test

U: Upper Specification Limit

L: Lower Specification Limit

Official Product	HV-32690/230/2SYGUYC	Customer Part No.		Data Sheet No.
	*****	*****		HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Mar.11 2022	Version of 1.3	Page 12/14

Packing Specification:

	HARVATEK	
CPN:		RoHs
P/N:		
		
HV-32690/230/2SYGUYC		
QTY:		CAT:
		HUE:
LOT NO:		REF:
		

Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Mar.11 2022	Version of 1.3	Page 13/14

Revision History

Revision	Page	Version No.	Revision Date
Initial Release		1.0	10-08-2021
Modify the surface position	4	1.1	10-18-2021
Modify the figure size	4	1.2	12-28-2021
Increase the center offset dimension	4	1.3	03-11-2022

Official Product	HV-32690/230/2SYGUYC	Customer Part No.	Data Sheet No.
	*****	*****	HV-32690/230/2SYGUYC
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Mar.11 2022	Version of 1.3	Page 14/14