










RoHS
Compliant

ZONE	ECN.N.O.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生財	2024.05.05




NOTES


1. CURRENT RATING: 24V & 5A MAX.
2. CONTACT RESISTANCE: 50mΩ MAX.
3. INSULATION RESISTANCE: 100MΩ MIN.
4. DIELECTRIC WITHSTANDING: 500V AC MIN.
5. DURABILITY: 5000 CYCLES MIN.
6. CONNECTOR MATING FORCES: 3~35N.
7. CONNECTOR UNMATING FORCES: 3~35N.
8. OPERATING TEMPERATURE: -25°C TO +85°C.




WHITE WATERPROOF RING



Not to install the waterproof ring shipment



Circuit Diagram



8	WATERPROOF RING	1	SILICONE, WHITE
7	GLUE	1	EPOXY, BLACK
6	BACK COVER	1	HIGH TEMPERATURE, BLACK
5	HOUSING	1	HIGH TEMPERATURE, BLACK
4	INNER BUSING	1	COPPER ALLOY, NICKEL PLATING
3	TERMINAL 3#	1	COPPER ALLOY, NICKEL UNDERPLATING OVERALL, Au PLATING ON SOLDER AREA
2	TERMINAL 2#	1	COPPER ALLOY, NICKEL UNDERPLATING OVERALL, Au PLATING ON THE WHOLE
1	TERMINAL 1#	1	COPPER ALLOY, NICKEL UNDERPLATING OVERALL, Au PLATING ON SOLDER AREA
ITEM	NAME	QTY	DESCRIPTION

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生財	DATE:	2024.05.05	SCALE	1:1
CHECK:	李宏鑫	DATE:	2024.05.05	MATERIAL	*
APPROVAL:	楊耀堂	DATE:	2024.05.05	DWG. NO.	
DRAWING NO.	ZB30008-03DBAP-B			SHEET	1/1

PART NAME	Ø2.0 WATERPROOF DC POWER JACK	TOLERANCE UNLESS	0.0±0.30	0.1±2°	UNIT: mm	
PART NO.	ZB30008-03DBAP-B	OTHERWISE SPECIFIED:	0.00±0.20	0.0°±1°		
			0.000±0.10	0.00°±0.5°		