

1		2		3		4		5		6		7		8	
REV ECN NO DESCRIPTION DESIGN APPROVAL DATE A1 NEW Replace frame 2020.06.12					ROHS		主要技术性能 1. 额定电负荷： 30V•5A； 2. 接 触 电 阻： ≤0.03 Ω； 3. 绝 缘 电 阻： ≥100M Ω； 4. 耐 压： AC500V (50Hz) /min； 5. 插 拔 力： 3~25N； 6. 寿 命： 5,000次。								
10.2±0.1 7.20±0.05±0.1 2.70±0.05 3.00±0.05 1.40±0.05X1.4 3.21±0.05 3.65±0.05 6.15±0.05 6.25±0.05 1.80±0.05 1.60±0.05 10.20±0.05 3.10±0.05 3.40±0.05 10.30±0.05 1.60±0.05 1.80±0.05 10.00±0.05 6.25±0.05 5.25±0.05 3.25±0.05 3.00±0.05 10.30±0.05 6.15±0.05 3.65±0.05 4.10±0.05 1.6X1.6 3-(2.0x0.8) 2-2.0X0.6 9C W 5 116 B T F X Model Definition Mould Number: XM04420 Needle Diameter:2.0 mm Fixing Method: Fixed Column Type Interface Method: Conventional Flared Opening Overall Length: 11.6mm Pin Position: 3 Pin Mounting Method: Horizontal (SMT) Product Series: DC Power Jacks 7 公头扣 1 磷铜带 t=0.10mm 镀镍 6 盖 脚 1 黄铜带 t=0.20mm 镀镍 5 弹片脚 1 磷铜带 t=0.30mm 镀银 4 插片脚 1 黄铜带 t=0.30mm 镀银 3 平 片 1 黄铜带 t=0.30mm 镀银 2 圆 针 1 黄铜带 t=0.30mm 镀镍 1 基 座 1 PPA 黑色 序号 名 称 数量 材 料 备 注 FIRST VIEW SCALE 1:1 UNIT mm SAMZO COMPONENTS Electronic switch and connector manufacturer The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM TITLE:: 大电流 卧式插件 5PIN带柱 DWG NO: 9CW5116-A4420 PART NO: 9CW5-20234420 MODEL NO: 9CW5116BTFX NAME: DC JACK															