


**DUAL TRANSISTOR (NPN+NPN)****APPLICATION**

This device is designed for general purpose amplifier applications

Marking :1C

MAXIMUM RATINGS ($T_a=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	50	V
V_{CEO}	Collector-Emitter Voltage	45	
V_{EBO}	Emitter-Base Voltage	6	
I_C	Collector Current-Continuous	100	mA
P_D	Power Dissipation	200	mW
$R_{\theta JA}$	Thermal Resistance. Junction to Ambient	625	$^{\circ}\text{C}/\text{W}$
T_J, T_{stg}	Operation Junction and Storage Temperature Range	-55~+150	$^{\circ}\text{C}$







**ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$ unless otherwise specified)**


Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=10\mu\text{A}, I_E=0$	50			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=1\text{mA}, I_B=0$	45			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=10\mu\text{A}, I_C=0$	6			V
Collector cut-off current	I_{CBO}	$V_{CB}=30\text{V}, I_E=0$			15	nA
Emitter cut-off current	I_{EBO}	$V_{EB}=4\text{V}, I_C=0$			15	
DC current gain*	h_{FE}	$V_{CE}=5\text{V}, I_C=2\text{mA}$	110		630	
Collector-emitter saturation voltage	$V_{CE(sat)(1)}$	$I_C=10\text{mA}, I_B=0.5\text{mA}$			0.25	V
	$V_{CE(sat)(2)}$	$I_C=100\text{mA}, I_B=5\text{mA}$			0.65	V
Base-emitter voltage	$V_{BE(1)}$	$V_{CE}=5\text{V}, I_C=2\text{mA}$	0.58		0.7	V
	$V_{BE(2)}$	$V_{CE}=5\text{V}, I_C=10\text{mA}$			0.77	V
Transition frequency	f_T	$V_{CE}=5\text{V}, I_C=20\text{mA}, f=100\text{MHz}$		200		MHz
Collector output capacitance	C_{ob}	$V_{CB}=10\text{V}, I_E=0, f=1\text{MHz}$		2		pF

*pulse test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycles $\leq 2.0\%$.




Typical Characteristics



**SOT-363 Package Outline Dimensions**


COMMON DIMENSIONS (UNITS OF MEASURE IS mm)			
	MIN	NORMAL	MAX
A	2.000	2.100	2.200
B	1.150	1.250	1.350
C	0.900	0.950	1.000
C1	0.500	0.550	0.600
D	2.100	2.300	2.500
L	0.220	0.360	0.500
b	0.200	0.250	0.400
h	0.020	0.050	0.100
e	0.650 TYPE		
θ_1	8° TYPE		
θ_2	8° TYPE		
θ_3	8° TYPE		
θ_4	8° TYPE		
θ	0~8° TYPE		

SOT-363 Embossed Carrier Tape




Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
SOT-363	2.25	2.55	1.20	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

SOT-363 Tape Leader and Trailer



SOT-363 Reel



Dimensions are in millimeter							
Reel Option	D	D1	D2	G	H	I	W1
7" Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	192x182x182	180,000 pcs	192x182x182	