




Transient Voltage Suppressors

Features

- 800 Watts Peak Pulse Power per Line ($t_p = 8/20\mu s$)
- Low Clamping Voltage
- Working Voltage: 15V
- Low Leakage Current



Absolute Maximum Ratings ($T_a = 25^\circ C$)

Parameter	Symbol	Value	Unit
Peak Pulse Current ($t_p = 8/20 \mu s$)	I_{PP}	28	A
ESD discharge (IEC61000-4-2) Air	ESD	± 30	KV
Contact		± 30	
Peak Pulse Power ($t_p = 8/20 \mu s$)	P_{PP}	800	W
Operation Temperature Range	T_j	- 55 to + 150	$^\circ C$
Storage Temperature Range	T_{stg}	- 55 to + 150	$^\circ C$



Characteristics at $T_a = 25^\circ C$

Parameter	Symbol	Min.	Typ.	Max.	Unit
Reverse Working Voltage	V_{RWM}			15	V
Reverse Breakdown Voltage $I_{BR} = 1 \text{ mA}$	$V_{(BR)R}$	16		18	V
Reverse Current at $V_R = 15 \text{ V}$	I_R			0.5	μA
Clamping Voltage $I_{PP} = 28A (t_p = 8/20 \mu s)$	V_C		30	35	V
Junction Capacitance at $V_R = 0 \text{ V}$, $f = 1 \text{ MHz}$	C_j		100	120	pF




Transient Voltage Suppressors


Capacitance Characteristics



VC-IPP




Power Derating Curve






DFN1006-2 Package Outline Drawing



COMMON DIMENSIONS (UNITS OF MEASURE IS mm)			
	MIN	NORMAL	MAX
A	0.550	0.600	0.650
B	0.950	1.000	1.050
C	0.450	0.500	0.550
D	0.450	0.500	0.550
E	0.200	0.250	0.300
F	0.450	0.500	0.550
G	0.200	0.250	0.300
L	0.200	0.250	0.300
e	0.650 TYPE		

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.60	0.024
Y1	0.50	0.020
Y2	0.30	0.012
Y3	0.80	0.032
Z	1.30	0.052