

SG series



Features

- ★ 超高压品
- ★ 105℃ 5000-10000Hrs




Specifications

item	Performance Characteristics	
Operating Temperature Range	-55~+105℃	
Rated Voltage Range	160~250vdc	
Capacitance Tolerance	±20%(120Hz,+20℃)	
Leakage Current(+20℃,max)	≤0.2CV or 500uA whichever is greater (After rated voltage applied for 2 minutes)	
Dissipation Factor(tanδ,at 20℃,120Hz)	Not exceed the value specified	
ESR(100KHz)	Not exceed the value specified	
Endurance 105℃,5000-10000h,at rated voltage	Capacitance Change	Within ±20% of the value before test
	Leakage Current	Not exceed the value specified
	ESR	Not exceed 150% of the value specified
	Dissipation Factor	Not exceed 150% of the value specified
Moisture Resistance Stored at 60℃,RH90~95%,1000h	Capacitance Change	Within ±20% of the value before test
	Leakage Current	Not exceed the value specified
	ESR	Not exceed 150% of the value specified
	Dissipation Factor	Not exceed 150% of the value specified

Frequency Coefficient for Ripple Current

Frequency	120Hz≤freq. < 1KHz	1KHz≤freq. < 10KHz	10KHz≤freq. < 100KHz	100KHz≤freq. < 300KHz
Coefficient	0.05	0.3	0.7	1



Size

Unit: mm

ΦDXL	ΦD+0.5 max.	a	F±0.5	Φd±0.05	
5X5-18	5	1	2	0.5	
5.5X5-18	5.5	1	2.5	0.5	
6.3X5-9	6.3	1	2.5	0.5/0.6	
6.3X11-20	6.3	1	2.5	0.6	
8X7P-15P	8	1	2.5	0.6	
8X7-20	8	1	3.5	0.6	
10X10-20	10	1	5	0.6	

料号	规格	系列	WV	CAP	LC	DF	ESR	SIZE	纹波
SG106M160F0800	SG160V10 8X8	SG	160	10	500	12	130	8X8	600