

SOREDE

索瑞達電子

深圳市索瑞达电子有限公司

承 认 书

SPECIFICATION FOR APPROVAL

客 户 名 称: 标 准
Customer Name : _____

客 户 料 号 :
Customer P/N: _____

产 品 名 称: 功率电感
Product Name: _____

索 瑞 达 料 号 :
Sorede P/N: SCD.5835.DYF系列

制造厂商 Manufacturer	
拟 制 Draft	黄小香
审 核 Check	符妃团 工程专用章
日 期 Date	2024-09-21

客户承认印章 Approval Signet	
日 期 Date	

地址:深圳市观澜镇福城街道新塘村8号源创园陆号A6栋3楼.

Address:3Rd Floor, Building A6, Yuanchuangyuanlu, No. 8 Xintang Village,
Fucheng Street, Guanlan Town, Shenzhen.

电话 Tel: 0755-29803356 传真 Fax: 0755-29803506

电子邮件 E-mail: sorde@vip.163.com

网址 http:// www.szsorede.com

Modify Resume

[illegible]

文件编号 File Number	SRD-WI-3655	版本号 Version Number	B	页码 page	2/9
---------------------	-------------	-----------------------	---	------------	-----

5、电性能参数表 Electrical Characteristics List

规格型号 Part NO.	电感量 Tolerance(μ H)	测试频率 Test Freq. (kHz/v)	直流电阻 DCR Max (Ω)	饱和电流 Isat (A)
SCD.5835.CYF1R0MT00	1.0	100 / 0.25	0.017	3.70
SCD.5835.CYF1R5MT00	1.5	100 / 0.25	0.020	3.50
SCD.5835.CYF1R8MT00	1.8	100 / 0.25	0.022	3.00
SCD.5835.CYF2R2MT00	2.2	100 / 0.25	0.026	2.85
SCD.5835.CYF2R5MT00	2.5	100 / 0.25	0.034	2.70
SCD.5835.CYF3R3MT00	3.3	100 / 0.25	0.040	2.40
SCD.5835.CYF3R9MT00	3.9	100 / 0.25	0.046	2.25
SCD.5835.CYF4R7MT00	4.7	100 / 0.25	0.052	1.90
SCD.5835.CYF5R6MT00	5.6	100 / 0.25	0.058	1.88
SCD.5835.CYF6R8MT00	6.8	100 / 0.25	0.071	1.87
SCD.5835.CYF8R2MT00	8.2	100 / 0.25	0.081	1.82
SCD.5835.DYF1R5MT00	1.5	100 / 0.25	0.024	3.50
SCD.5835.DYF2R2MT00	2.2	100 / 0.25	0.030	2.85
SCD.5835.DYF3R3MT00	3.3	100 / 0.25	0.042	2.40
SCD.5835.DYF4R7MT00	4.7	100 / 0.25	0.059	1.90
SCD.5835.DYF6R8MT00	6.8	100 / 0.25	0.073	1.87
SCD.5835.DYF100KT00	10	100 / 0.25	0.094	1.78
SCD.5835.DYF120KT00	12	100 / 0.25	0.126	1.60
SCD.5835.DYF150KT00	15	100 / 0.25	0.139	1.58
SCD.5835.DYF180KT00	18	100 / 0.25	0.160	1.30
SCD.5835.DYF220KT00	22	100 / 0.25	0.192	1.29
SCD.5835.DYF270KT00	27	100 / 0.25	0.242	1.10
SCD.5835.DYF330KT00	33	100 / 0.25	0.325	0.95
SCD.5835.DYF390KT00	39	100 / 0.25	0.369	0.92
SCD.5835.DYF470KT00	47	100 / 0.25	0.436	0.82
SCD.5835.DYF560KT00	56	100 / 0.25	0.553	0.80
SCD.5835.DYF680KT00	68	100 / 0.25	0.628	0.76
SCD.5835.DYF820KT00	82	100 / 0.25	0.785	0.67

※公差Tolerance: N:±30%、M:±20%、K:±10%.

※工作温度Operating temperature rang: -40 ℃ to +105℃ (Including Self-heating)

※储存温度Storage temperature rang: -40 ℃ to +125℃

Isat电流: 指使电感量比初始值下降10%Max (The rated DC current is that which cause at 10%Max inductance reduction from the initial value) 。

文件编号 File Number	SRD-WI-3655	版本号 Version Number	B	页码 page	3/9
电性能参数表 Electrical Characteristics List					
规格型号 Part NO.	电感量 Tolerance(μ H)	测试频率 Test Freq. (kHz/v)	直流电阻 DCR Max (Ω)	饱和电流 Isat (A)	
SCD.5835.DYF101KT00	100	100 / 0.25	0.848	0.62	
SCD.5835.DYF121KT00	120	100 / 0.25	1.030	0.60	
SCD.5835.DYF151KT00	150	100 / 0.25	1.44	0.48	
SCD.5835.DYF181KT00	180	100 / 0.25	1.64	0.43	
SCD.5835.DYF221KT00	220	100 / 0.25	2.08	0.37	
SCD.5835.DYF271KT00	270	100 / 0.25	2.46	0.33	
SCD.5835.DYF331KT00	330	100 / 0.25	3.71	0.30	
SCD.5835.DYF391KT00	390	100 / 0.25	4.24	0.26	
SCD.5835.DYF471KT00	470	100 / 0.25	4.42	0.24	
SCD.5835.DYF561KT00	560	100 / 0.25	4.68	0.22	
SCD.5835.DYF681KT00	680	100 / 0.25	6.42	0.21	
SCD.5835.DYF821KT00	820	100 / 0.25	7.36	0.18	
SCD.5835.DYF102KT00	1000	100 / 0.25	9.73	0.17	
SCD.5835.DYF152KT00	1500	100 / 0.25	15.0	0.15	
SCD.5835.DYF222KT00	2200	100 / 0.25	24.7	0.12	
SCD.5835.DYF392KT00	3900	100 / 0.25	42.0	0.11	
SCD.5835.DYF562KT00	5600	100 / 0.25	59.0	0.09	
SCD.5835.DYF123KT00	12000	100 / 0.25	124.0	0.06	

※公差Tolerance: N:±30%、M:±20%、K:±10%.


※工作温度Operating temperature rang: -40 ℃ to +105℃ (Including Self-heating)

※储存温度Storage temperature rang: -40 ℃ to +125℃

Isat电流: 指使电感量比初始值下降10%Max (The rated DC current is that which cause at 10%Max inductance reduction from the initial value) 。


6、产品包装 Packaging

1) 载带包装示意图 Tape packing diagram




ITEM	W	A0	B0	K0	P	E	F	D0	P0	P2	T
DIM	12.00	5.90	5.40	3.90	8.00	5.50	1.75	1.50	4.00	2.00	0.40
TOLE	±0.3	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	+0.1	±0.1	±0.1	±0.05

2) 卷盘包装示意图 Tape packing diagram




A	330±0.5
B	100±0.5
C	13.5±0.5
W	12.5±0.5

3) 卷盘包装示意图 Tape packing diagram




4) 剥离强度要求Peeling required


- ①F 力大小： 20~100g;
- ②面带剥离角度： 165°~180°。



5) 包装数量 Packing quantity



项目 (Project)	数量 (PCS)	尺寸规格 (Size:mm)
盘(Reel)	2000	13"
内盒 (Inner box)	8000	340mm*340mm*65mm
外箱 (Out box)	24000	360mm*360mm*235mm

文件编号 File Number	SRD-WI-3655	版本号 Version Number	B	页码 page	6/9
7.RELIABILITY TEST METHOD					
MECHANICAL					
TEST ITEM	SPECIFICATION	TEST DETAILS			
Substrate bending	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage or electrical damage.	<p>The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm.(keep time 30 seconds)</p> <p>PCB dimension shall the page 7/9</p> <p>F(Pressurization)</p>  <p>figure-1</p>			
Vibration	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage.	<p>The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each.</p> <p>(A total of 6 hours)</p>			
Solderability	New solder More than 90%	<p>Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150℃ and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±2℃.</p> <p>More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.</p>			

文件编号 File Number	SRD-WI-3655	版本号 Version Number	B	页码 page	7/9
---------------------	-------------	-----------------------	---	------------	-----

MECHANICAL		
TEST ITEM	SPECIFICATION	
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	<p>Temperature profile of reflow soldering</p> <p>The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time.</p> <p>The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.</p>

ELECTRICAL		
TEST ITEM	SPECIFICATION	TEST DETAILS
Insulation resistance	There shall be no other damage or problems.	<p>DC 100V voltage shall be applied across this sample of top surface and the terminal.</p> <p>The insulation resistance shall be more than $1 \times 10^8 \Omega$.</p>
Dielectric withstand voltage	There shall be no other damage or problems.	AC 100V voltage shall be applied for 1 minute across the top surface and the terminal of this sample
Temperature characteristics	$\Delta L/L 20^\circ\text{C} \leq \pm 10\%$ $0 \sim 2000 \text{ ppm}/^\circ\text{C}$	<p>The test shall be performed after the sample has stabilized in an ambient temperature of -40 to $+105^\circ\text{C}$, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be $\Delta L/L 20^\circ\text{C} \leq \pm 10\%$.</p>

ENVIROMENT CHARACTERISTICS

TEST ITEM	SPECIFICATION																
High temperature storage	<div> <div>△ L/Lo≤±5%</div> <div>There shall be no mechanical damage.</div> </div>	<div> <div>The sample shall be left for 500hours in an atmospere with a temperature of 105±2℃ and a normal humidity.</div> <div>Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.</div> </div>															
Low temperature storage	<div> <div>△ L/Lo≤±5%</div> <div>There shall be no mechanical damage.</div> </div>	<div> <div>The sample shall be left for 500 hours in an atmosphere with a temperature of -40±3℃.</div> <div>Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.</div> </div>															
Change of temperature	<div> <div>△ L/Lo≤±5%</div> <div>There shall be no other dama-ge of problems</div> </div>	<div> <div>The sample shall be subject to 5 continuos cycles, such as shown in the table 2 below and then it shall be subjected to standard stmospheric conditions for 1 hour, after which measurement shall be made.</div> <div> <div>table 2</div> <table> <tr> <th></th><th>Temperature</th><th>Duration</th></tr> <tr> <td>1</td><td> <div> <div>- 40±3℃</div> <div>(Thermostat No.1)</div> </div> </td><td>10 min.</td></tr> <tr> <td>2</td><td> <div> <div>Standard atmospheric</div> </div> </td><td> <div> <div>5 sec. or less</div> <div>No.1→No.2</div> </div> </td></tr> <tr> <td>3</td><td> <div> <div>105±2℃</div> <div>(Thermostat No.2)</div> </div> </td><td>30 min.</td></tr> <tr> <td>4</td><td> <div> <div>Standard atmospheric</div> </div> </td><td> <div> <div>5 sec. or less</div> <div>No.2→No.1</div> </div> </td></tr> </table> </div> </div>		Temperature	Duration	1	<div> <div>- 40±3℃</div> <div>(Thermostat No.1)</div> </div>	10 min.	2	<div> <div>Standard atmospheric</div> </div>	<div> <div>5 sec. or less</div> <div>No.1→No.2</div> </div>	3	<div> <div>105±2℃</div> <div>(Thermostat No.2)</div> </div>	30 min.	4	<div> <div>Standard atmospheric</div> </div>	<div> <div>5 sec. or less</div> <div>No.2→No.1</div> </div>
	Temperature	Duration															
1	<div> <div>- 40±3℃</div> <div>(Thermostat No.1)</div> </div>	10 min.															
2	<div> <div>Standard atmospheric</div> </div>	<div> <div>5 sec. or less</div> <div>No.1→No.2</div> </div>															
3	<div> <div>105±2℃</div> <div>(Thermostat No.2)</div> </div>	30 min.															
4	<div> <div>Standard atmospheric</div> </div>	<div> <div>5 sec. or less</div> <div>No.2→No.1</div> </div>															
Moisuture storage	<div> <div>△ L/Lo≤±5%</div> <div>There shall be no mechanical damage.</div> </div>	<div> <div>The sample shall be left for 500 hours in a temperature of 40±2℃ and a humidity(RH) of 90~ 95%.</div> <div>Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.</div> </div>															

Test conditions :

The sample shall be reflow soldered onto the printed circuit board in every test.

文件编号 File Number	SRD-WI-3655	版本号 Version Number	B	页码 page	9/9
8、注意事项 Note					
<p>①本承认书保证我司产品作为一个单体时的质量情况。当我司产品被安装到贵司产品上时，请保证贵司的产品已根据贵司的规范进行了有效评估和确认。</p> <p>This product specification guarantees the quality of our product as a single unit. Please make sure that your product is evaluated and confirmed against your specifications when our product is mounted to your product.</p> <p>②如果贵司对我司产品的使用已超过了本承认书所界定的产品功能，那么对于由此引发的失效，我司将不予保证。</p> <p>We cannot warrant against failure caused by any use of our product that deviates from the intended use as described in this product specification.</p> <p>③为了保持终端电极的焊接性，并使包装材料保持良好状态，必须控制储存区的温度和湿度。</p> <p>To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled.</p> <p>※建议的条件：-10 ~ +40℃，30~70%RH。</p> <p>Recommended conditions: -10 ~ +40℃，30~70%RH.</p> <p>※储存超过六个月的，应在实际使用前进行焊接检验。</p> <p>In case of storage over 6 months, solderability shall be checked before actual usage.</p> <p>※即使在理想的储存条件下，产品的可焊性也随着时间的推移而降低。因此，产品应从交货时算起，建议8个月之内使用完。</p> <p>Even under ideal storage conditions, the weldability of the product decreases over time. therefore, the product should be From the time of delivery, it is recommended that it be used within 8 months.</p> <p>④本承认书在客户收到30 天之内，必须签章返回，逾期视为默认。</p> <p>The Specification Approval should be sent back to the supplier with customer's chop on it within 30 days after receiving it, or we will take it as approved by customer's automatically.</p> <p>⑤如有特殊规格要求，请事前联络我司技术部人员。</p> <p>In case of special specifications please contact our technical department prior staff.</p>					