


DIMENSION (UNIT:mm)



A	A1	B	C	C1	D	E
4.00 ± 0.15	4.90 Max	3.10 ± 0.10	2.60 ± 0.10	2.83 ± 0.10	1.35 ± 0.40	1.25 Typ.

ELECTRICAL SPECIFICATION


MEAS. ITEM	SPEC.				TEST FREQ.
Z1	30	Ω	$\pm$	20%	25MHz/100mV
Z2	47	Ω	$\pm$	20%	100 MHz/100mV
Rdc	0.006	Ω	Max.		
Idc	13	A	Max.		
● HP 4338A MILLIOHMMETER ● Agilent E4991A RF IMPEDANCE/MATERIAL ANALYZER					

TEST DATA

MEAS.	A	A1	B	C	C1	Z1	Z2	RDC
ITEM	(m/m)	(m/m)	(m/m)	(m/m)	(m/m)	(Ω)	(Ω)	(Ω)
SPEC.	4.00 ± 0.15	4.90 Max.	3.10 ± 0.10	2.60 ± 0.10	2.83 ± 0.10	30 $\pm$ 20%	47 $\pm$ 20%	0.006 MAX.
TEST FREQ.						25 MHz	100 MHz	
1	4.05	4.53	3.08	2.60	2.80	33.10	45.40	0.00052
2	4.00	4.54	3.09	2.58	2.80	32.80	45.00	0.00053
3	4.03	4.55	3.09	2.61	2.80	32.90	44.90	0.00054
4	4.03	4.53	3.09	2.58	2.80	33.10	45.20	0.00055
5	4.03	4.58	3.07	2.59	2.82	33.10	45.30	0.00052
6	4.05	4.55	3.09	2.59	2.81	32.90	44.90	0.00056
7	4.03	4.56	3.08	2.58	2.81	32.80	44.90	0.00053
8	4.03	4.55	3.10	2.61	2.80	32.60	44.80	0.00046
9	4.04	4.55	3.09	2.59	2.82	32.90	44.90	0.00053
10	4.03	4.55	3.08	2.58	2.83	33.60	44.80	0.00052
AVG.	4.04	45.49	3.09	2.59	2.81	33.00	45.00	0.00053
R	0.02	0.05	0.03	0.03	0.03	1.00	0.60	0.00007

IMPEDANCE VS. FREQUENCY CHARACTERISTIC

PACKAGING INFORMATION




Carrier tape material : Polystyrene (Dimension in m/m)

TYPE	W	P	E	F	D	D1	Po	Po10	P2	Ao	Bo	Ko	t
453225	12 ±0.10	8 ±0.10	1.75 ±0.10	5.5 ±0.05	1.5 +0.1 -0	1.5 +0.1 -0	4 ±0.10	40 ±0.20	2 ±0.05	3.3 ±0.10	4.8 ±0.10	3.1 ±0.10	0.28 ±0.05


● Reel dimensions and packaging quantities

Material of Reel is Polystyrene (Dimensions in mm)



● Packing Quantity

Φ330mm Reel : 500 PCS / Reel



TYPE	A	B	C	G	N	T
7"x12m/m	178±1.0	19±0.5	13.3±0.5	13.7±0.5	60±0.5	16.1±0.5
330x16m/m	330±1.0	19±0.5	13.2±0.5	13.7±0.5	100±1.	16.1±0.5