


### SCHEMATIC(NON-SHORTING)



|     |           |                      |      |                          |  |                                                                                                  |       |      |  |
|-----|-----------|----------------------|------|--------------------------|--|--------------------------------------------------------------------------------------------------|-------|------|--|
| 8   |           |                      |      |                          |  | TOLERANCE                                                                                        |       |      |  |
| 7   | PRESS BAR | NYLON+F.G+94V0(PA9T) | 1    | BLACK                    |  | UNLESS SPECIFIED                                                                                 |       |      |  |
| 6   | SPRING    | STEEL WIRE           | 1    | NATURAL                  |  | WITHIN : ±0.2mm                                                                                  | A     |      |  |
|     | CONTACT   | COPPER STRIP         | 1    | Ag PLATED                |  | OVER : ±0.2mm                                                                                    | ISSUE | DATE |  |
| 4   | TERMINAL  | COPPER STRIP         | 3    | Ag PLATED OVER Ni PLATED |  | TITLE : VERTICAL SLIDE SWITCH                                                                    |       |      |  |
| 3   | CASE      | NYLON+F.G+94V0(PA9T) | 1    | BLACK                    |  | UNIT : mm                                                                                        |       |      |  |
| 2   | COVER     | SUS                  | 1    | NATURAL                  |  | SCALE: 3 : 1                                                                                     |       |      |  |
| 1   | KNOB      | NYLON+F.G+94V0(PA9T) | 1    | BLACK                    |  | MODEL: SS 12D10S5-WJ                                                                             |       |      |  |
| NO. | PARTS     | MATERIALS            | Q'TY | FINISH                   |  |  深圳市首韩科技有限公司 |       |      |  |
|     |           |                      |      |                          |  | DRWG NO.: HR-DR-SS12D10-00                                                                       |       |      |  |
|     |           |                      |      |                          |  | DWN. 李春风                                                                                         |       |      |  |
|     |           |                      |      |                          |  | CHK'D 钟华华                                                                                        |       |      |  |
|     |           |                      |      |                          |  | APPD. 罗孝金                                                                                        |       |      |  |



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

## 承 认 书

### SPECIFICATION FOR APPROVAL

产品编码  
Material code:

产品名称 Project:

拨动开关

规格型号 Part No:

SS12D10G5-WJ

贵公司承认印 Approval signatures

| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

日期 Date:

|             |     |                                                                                      |
|-------------|-----|--------------------------------------------------------------------------------------|
| 拟制/Drawn    | 李春风 |  |
| 审核/Check    | 钟华华 |                                                                                      |
| 批准/Approved | 罗孝金 |                                                                                      |

|                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                |                                                                     |
|----------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------|
|  深圳市首韩科技有限公司 |                                                                                                                                                                                                                                                                                                                                                                                   | 文件编号                                                                                                                                                                                                                                           |                                                                     |
|                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                   | 发布日期                                                                                                                                                                                                                                           | 2020年6月24日                                                          |
| SPECIFICATION 规格书                                                                            |                                                                                                                                                                                                                                                                                                                                                                                   | 第2版                                                                                                                                                                                                                                            | 1of2                                                                |
| 产品名称:拨动开关                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                   | 产品型号: SS12D10G5-WJ                                                                                                                                                                                                                             |                                                                     |
| 1:GENERAL SPECIFICATION 基本事项                                                                 |                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                |                                                                     |
| 1.1                                                                                          | RATING (额定值): AC 125V 2A                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                |                                                                     |
| 1.2                                                                                          | PRACTICAL TEMPERATURE RANEG: - 25℃~+70℃.<br>使用温度范围: 在-25℃~+70℃溫度內使用.                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                |                                                                     |
| 1.3                                                                                          | STANDARD ATMOSPHEIC CONDITIONS :<br>UNLESS OTHERWISE SPECIFIED. THE STANDARD RANGE OF ATMOSPHERIC<br>CONDITIONS FOR MAKING MEASUREMENTS AND TESTS ARE AS FOLLOWS:<br>(1) AMBIENT TEMPERATURE : 5℃ TO 35℃;<br>(2) RELATIVE HUMIDITY : 45% TO 85%;<br>(3) AIR PRESSURE : 86Kpa TO 106Kpa.<br>测试标准状态: 在沒有指定的情況下测试温度, 湿度, 气压如下:<br>(1) 温度为5~35℃; (2) 湿度为45%~85%; (3) 气压为86Kpa~106Kpa. |                                                                                                                                                                                                                                                |                                                                     |
| 2. ELECTRICAL CHARACTERISTICS (电气性能规格):                                                      |                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                |                                                                     |
| ITEM                                                                                         | 项目                                                                                                                                                                                                                                                                                                                                                                                | TEST CONDITIONS 测试条件                                                                                                                                                                                                                           | PERFORMANCE (DATA) 规格(数据)                                           |
| 2.1                                                                                          | CONTACT<br>RESISTANCE<br>接触电阻                                                                                                                                                                                                                                                                                                                                                     | MEASURED AT 1KHz SMALL CURRENT(100 mA OR LESS)<br>在1KHz微小电流(100mA 以下)测试.                                                                                                                                                                       | 100mΩ MAX.<br>100毫欧以下.                                              |
| 2.2                                                                                          | INSULATION<br>RESISTANCE<br>绝缘电阻                                                                                                                                                                                                                                                                                                                                                  | APPLY A VOLTAGE OF 100V DC FOR 1 MIN.<br>THE FOLLOWING CONTACE TEST METHOD:<br>(1)BETWEEN BODY AND CONDUCTOR.<br>(2) BETWEEN CONDUCTORS NOT TO BE CONTAC.<br>输入100V DC电压1分钟, 按以下接触方法测试:<br>(1)接触端子之间.<br>(2)胶座体和排脚之间.                          | 100MΩ MIN.<br>100兆欧以上.                                              |
| 2.3                                                                                          | IELECTRIC<br>STRENGTH<br>耐电压                                                                                                                                                                                                                                                                                                                                                      | AC 500V(50-60Hz) FOR 1 MIN TRIP CURRENT:0.5mA<br>THE FOLLOWING CONTACE TEST METHOD:<br>(1)BETWEEN TERMINALS.<br>(2) BETWEEN INDIVIDUAL TERMINALS AND FRAME.<br>输入AC500V(50-60Hz) 电压, 1分钟感度电流为0.5mA,<br>接触测试方法如下:<br>(1)接触端子之间.<br>(2)外壳体和排脚之间. | WITHOUT DAMAGE TO<br>PARTS ARCING OR<br>BREAKDOWN ETC.<br>沒有绝缘破坏等异常 |
| 3 .MECHANICAL CHARACTERISTICS (机械性能规格)                                                       |                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                |                                                                     |
| ITEM                                                                                         | 项目                                                                                                                                                                                                                                                                                                                                                                                | TEST CONDITIONS 测试条件                                                                                                                                                                                                                           | PERFORMANCE (DATA) 规格(数据)                                           |
| 3.1                                                                                          | OPERATION<br>FORCE<br>动作力                                                                                                                                                                                                                                                                                                                                                         | LATERAL PUSH (侧向推动)                                                                                                                                                                                                                            | PUSH FORCE (按压力度):<br>250gf±100gf                                   |
| 3.2                                                                                          | TRAVEL TO<br>CLOSURE<br>动作行程                                                                                                                                                                                                                                                                                                                                                      | IN THE HORIZONTAL DIRECTION SWITCH HANDLE<br>OPRATION, WITH AN EQUAL TO 2TIMES THE THRUST OF<br>THE SWITSH FORM ONE POSITION TO THE NEXT GEAR,<br>MOVING DISTANCE MEASURING HANDLE.<br>在开关推柄运行的水平方向, 以一个等于2倍推力使开关从<br>一个档位运动到下一档位, 测量推柄的移动距离.  | 2.2mm±0.2mm                                                         |
| 3.3                                                                                          | STEM<br>STRENGTH<br>操作部(柄)<br>强度                                                                                                                                                                                                                                                                                                                                                  | AND ALONG THE RUNNING DIRECTION AT APEX HANDLE(<br>500gf)ON THESTRENGTH TEST, TIME IS 30 SECONDS.<br>在推柄的先端沿运行方向加上(500gf)力度测试, 时间为<br>30秒.                                                                                                     | 外观无异常, 满足于机械,<br>电气性能                                               |

|                                                                                      |                              |                                                                                                                                                                                                                                                    |                    |                                                                                                                            |            |
|--------------------------------------------------------------------------------------|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------|------------|
|  首韩® |                              | 深圳市首韩科技有限公司                                                                                                                                                                                                                                        |                    | 文件编号                                                                                                                       | 2020年6月24日 |
|                                                                                      |                              |                                                                                                                                                                                                                                                    |                    | 发布日期                                                                                                                       |            |
| SPECIFICATION 规格书                                                                    |                              |                                                                                                                                                                                                                                                    |                    | 第2版                                                                                                                        | 2of2       |
| 产品名称: 拨动开关                                                                           |                              |                                                                                                                                                                                                                                                    | 产品型号: SS12D10G5-WJ |                                                                                                                            |            |
| 4. DURABILITY(耐久性):                                                                  |                              |                                                                                                                                                                                                                                                    |                    |                                                                                                                            |            |
| ITEM 项目                                                                              |                              | TEST CONDITIONS 测试条件                                                                                                                                                                                                                               |                    | PERFORMANCE (DATA) 规格(数据)                                                                                                  |            |
| 4.1                                                                                  | LIFE TEST<br>寿命试验            | AN ACTUATOR SHALL BE WITH A THRUST OF NO GREAT THAN 1 TIMES SWITH POWER TO 3000 CYCLES AT A SPEED OF 30 CYCLES FOR 1 MIN.<br>操作者以每分钟30次的频率, 施加不大于开关1倍的推力做3000次无负荷测试.                                                                               |                    | 1)CONTACT RESISTANCE SHALL BE 500mΩ MAX.<br>2)LIFETIME:3000 CYCLES<br>1) 接触电阻不超于500mΩ .<br>2) 寿命:3000次                     |            |
| 4.2                                                                                  | HEAT TEST<br>耐热实验            | THE SWITCH SHALL BE STORED AT A TEMPERATURE OF 85±2℃ FOR 96 HOURS.AND THEN IT SHALL BE SUBJECTED TO THE CONTROLLED RECOVERY CONDITIONS FOR 1 HOUR AFTER WHICH MEASUREMENT SHALL BE MADE.<br>放置在温度85±2℃中96小时后, 再放置正常室温中1小时后测定.                      |                    | THERE SHALL BE NO DAMAGE ONAPPEARANCE. MECHANICAL AND ELECTRICAL CHARACTERISTICS SHALL BE SATISFIED.<br>外观无异常, 满足于机械, 电气性能 |            |
| 4.3                                                                                  | COLD TEST<br>耐冷实验            | THE SWITCH SHALL BE STORED AT A TEMPERATURE OF-25±3℃ FOR 96 HOURS.AND THEN IT SHALL BE SUBJECTED TO THE CONTROLLED RECOVERY CONDITIONS FOR 1 HOUR AFTER WHICH MEASUREMENT SHALL BE MADE.<br>放置在温度-25±3℃中96小时后, 再放置正常室温中1小时后测定.                     |                    |                                                                                                                            |            |
| 4.4                                                                                  | HUMIDITY TEST<br>潮湿实验        | THE SWITCH SHALL BE STORED AT A TEMPERATURE OF 40±2℃ AND A HUMIDITY OF 80% TO 85% FOR 96 Hr. THEN THE JACK SHALL BE MAINTAINED AT STANDARD ATMOSPHERIC CONDITION FOR 1 Hr FOR OTHER PROCEDURES.<br>放置在40±2℃相对湿度为80~85%环境中96小时后, 再将样品放在正常室温中1小时后测定. |                    |                                                                                                                            |            |
| 4.5                                                                                  | SOLDERING CONDITIONS<br>焊锡条件 | HANDSOLDERING手焊:<br>1) DIVCE工具: SOLDER IRON电烙铁.<br>A .350°C MAX. ,2secMax<br>B.270°C MAX. ,4secMax                                                                                                                                                 |                    | THERESHALLBENO DAMAGEONAPPEARANCE. MECHANICALAND ELECTRICAL CHARACTERISTICSSHALL BESATISFIED.<br>外观无异常, 满足于机械, 电气性能        |            |