









技术参数:

1. 做用温度: -25~+85℃;
2. 额定负荷: DC 12V 50mA;
3. 接触电阻: ≤50mΩ;
4. 绝缘电阻: ≥100MΩ;
5. 耐 压: AC250V (50Hz)/min;
6. 动 作 力: 260±50g;
7. 使用寿命: 100000次;



电路图

Part NO.	A	H 高度
TC-0513-3.8-260G	2.5	3.8
TC-0513-4.3-260G	2.5	4.3
TC-0513-4.5-260G	2.5	4.5
TC-0513-5.0-260G	2.3	5.0
TC-0513-5.5-260G	2.3	5.5
TC-0513-6.0-260G	2.3	6.0
TC-0513-6.5-260G	2.3	6.5
TC-0513-7.0-260G	2.3	7.0
TC-0513-8.5-260G	2.2	8.5
TC-0513-9.0-260G	2.2	9.0
TC-0513-9.5-260G	2.2	9.5
.....	...	...
TC-0513-11.0-260G	2.0	11.0
TC-0513-12.0-260G	2.0	12.0

5	嵌件	1	H62Y 黄铜 T=0.30	Ag	
4	底座	1	PPA	黑	
3	簧片	1	不锈钢		
2	盖板	1	冷轧钢带	Cu/Sn	
1	按钮	1	PPA	黑	
序号	名称	数量	材料	镀层/颜色	备件

			GENERAL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	轻触开关 (SMT 4.5x4.5mm)	版本 REV.	A
			X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	TC-0513-NH-260G	单 位 UNITS	mm
1	初版发行		X. XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					