



REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:PP BLACK
b.SPRING:SPRING WIRE
c.TERMINAL:BRASS
(SURFACE PLATING: NI-PLATING)
SEE ORDERING INFORMATION
2.ELECTRIC:
a.DIELECTNIC VOLTAGE: 270V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-18650-B1AJ025-150

线长 (MM)



PLATING:
A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

电池盒

电池型号

SMT 180° TYPE



3	TERMINAL	2	BRASS	Ni-Plating
2	SPRING	2	SPRING WIRE	Ni-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2024-07-27	TITLE: 电池盒BH-18650-2J (22#线长150mm剥皮上锡3mm)	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-07-27		
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2024-07-27	PART NO.: BH-18650-B1AJ025-150	
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW: ④ ③	DRAW NO.:WD-CP-0409	
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY		